

Part number A10467 Polypropylene vertical band set for coated steel pipe (ivory) Units (mm)

Size code	Size (diameter size x shank length L)	Applicable pipe outer diameter	Bracket pipe diameter	Tightening bolt Dia. x Length	Anchor pitch
1484	C15× 50L	25.7	16	M6×30	44
1499	C15× 75L	25.7	16	M6×30	44
1501	C15× 100L	25.7	16	M6×30	44
1516	C15× 150L	25.7	16	M6×30	44
1535	C20× 50L	31.2	16	M6×30	44
1540	C20× 75L	31.2	16	M6×30	44
1554	C20× 100L	31.2	16	M6×30	44
1569	C20× 150L	31.2	16	M6×30	44
1573	C25× 50L	37.6	16	M6×30	44
1588	C25× 75L	37.6	16	M6×30	44
1592	C25× 100L	37.6	16	M6×30	44
1605	C25× 150L	37.6	16	M6×30	44

Part number A10467 Polypropylene vertical band set for copper pipe (white) Units (mm)

Size code	Size (diameter size x shank length L)	Applicable pipe outer diameter	Bracket pipe diameter	Tightening bolt Dia. x Length	Anchor pitch
1610	TW-1× 50L	15.88	16	M6×30	44
1624	TW-1× 65L	15.88	16	M6×30	44
1639	TW-1× 75L	15.88	16	M6×30	44
1643	TW-1× 100L	15.88	16	M6×30	44
1658	TW-1× 125L	15.88	16	M6×30	44
1662	TW-1× 150L	15.88	16	M6×30	44
1677	TW-1× 200L	15.88	16	M6×30	44
1681	TW-5× 50L	22.22	16	M6×30	44
1696	TW-5× 65L	22.22	16	M6×30	44
1709	TW-5× 75L	22.22	16	M6×30	44
1713	TW-5× 100L	22.22	16	M6×30	44
1728	TW-5× 125L	22.22	16	M6×30	44
1732	TW-5× 150L	22.22	16	M6×30	44
1747	TW-5× 200L	22.22	16	M6×30	44
1751	TW-7× 50L	28.58	16	M6×30	44
1766	TW-7× 65L	28.58	16	M6×30	44
1785	TW-7× 75L	28.58	16	M6×30	44
1790	TW-7× 100L	28.58	16	M6×30	44
1802	TW-7× 125L	28.58	16	M6×30	44
1817	TW-7× 150L	28.58	16	M6×30	44
1821	TW-7× 200L	28.58	16	M6×30	44

Part number A10467 Polypropylene vertical band set for coated copper pipe (white) Units (mm)

Size code	Size (diameter size x shank length L)	Applicable pipe outer diameter	Bracket pipe diameter	Tightening bolt Dia. x Length	Anchor pitch
1836	P20× 50L	31.0	16	M6×30	44
1855	P20× 65L	31.0	16	M6×30	44
1860	P20× 75L	31.0	16	M6×30	44
1874	P20× 100L	31.0	16	M6×30	44
1889	P20× 125L	31.0	16	M6×30	44
1893	P20× 150L	31.0	16	M6×30	44
1906	P20× 200L	31.0	16	M6×30	44

Part number A10467 Polypropylene vertical band set for VP pipe (beige) Units (mm)

Size code	Size (diameter size x shank length L)	Applicable pipe outer diameter	Bracket pipe diameter	Tightening bolt (D x L)	Anchor pitch
1925	A40× 50L	48.0	16	M6×30	44
1930	A40× 65L	48.0	16	M6×30	44
1944	A40× 75L	48.0	16	M6×30	44
1959	A40× 100L	48.0	16	M6×30	44
1963	A40× 125L	48.0	16	M6×30	44
1978	A40× 150L	48.0	16	M6×30	44
1982	A40× 200L	48.0	16	M6×30	44
1997	A50× 50L	60.0	16	M6×30	44
2001	A50× 65L	60.0	16	M6×30	44
2016	A50× 75L	60.0	16	M6×30	44
2035	A50× 100L	60.0	16	M6×30	44
2040	A50× 125L	60.0	16	M6×30	44
2054	A50× 150L	60.0	16	M6×30	44
2069	A50× 200L	60.0	16	M6×30	44
2088	A65× 65L	76.0	20	M8×40	64
2092	A65× 75L	76.0	20	M8×40	64
2105	A65× 100L	76.0	20	M8×40	64
2110	A65× 125L	76.0	20	M8×40	64
2124	A65× 150L	76.0	20	M8×40	64
2139	A65× 200L	76.0	20	M8×40	64
2158	A80× 65L	89.0	20	M8×40	64
2162	A80× 75L	89.0	20	M8×40	64
2177	A80× 100L	89.0	20	M8×40	64
2181	A80× 125L	89.0	20	M8×40	64
2196	A80× 150L	89.0	20	M8×40	64
2209	A80× 200L	89.0	20	M8×40	64
2228	A100× 65L	114.0	20	M8×40	64
2232	A100× 75L	114.0	20	M8×40	64
2247	A100× 100L	114.0	20	M8×40	64
2251	A100× 125L	114.0	20	M8×40	64
2266	A100× 150L	114.0	20	M8×40	64
2285	A100× 200L	114.0	20	M8×40	64

Part number A10467 Polypropylene vertical band set for VP pipe (white) Units (mm)

Size code	Size (diameter size x shank length L)	Applicable pipe outer diameter	Bracket pipe diameter	Tightening bolt (D x L)	Anchor pitch
2290	VW20× 50L	26.0	16	M6×30	44
2302	VW20× 65L	26.0	16	M6×30	44
2317	VW20× 75L	26.0	16	M6×30	44
2321	VW20× 100L	26.0	16	M6×30	44
2336	VW20× 125L	26.0	16	M6×30	44
2355	VW20× 150L	26.0	16	M6×30	44
2360	VW20× 200L	26.0	16	M6×30	44
2374	VW25× 50L	32.0	16	M6×30	44
2389	VW25× 65L	32.0	16	M6×30	44
2393	VW25× 75L	32.0	16	M6×30	44
2406	VW25× 100L	32.0	16	M6×30	44
2425	VW25× 125L	32.0	16	M6×30	44
2430	VW25× 150L	32.0	16	M6×30	44
2444	VW25× 200L	32.0	16	M6×30	44
2459	VW32× 50L	38.0	16	M6×30	44
2463	VW32× 65L	38.0	16	M6×30	44
2478	VW32× 75L	38.0	16	M6×30	44
2482	VW32× 100L	38.0	16	M6×30	44
2497	VW32× 125L	38.0	16	M6×30	44
2500	VW32× 150L	38.0	16	M6×30	44
2514	VW32× 200L	38.0	16	M6×30	44

Polypropylene T-bracket

Mounting brackets for raised pipes

Units (mm)

Part number	Size code	L	Color
A10507	0017	35	White
A10508	0014	35	Gray
A10509	0011	35	Ivory

