

ACRYLIC RESIN LEVEL

Special Orders Available

Please request for a quote.

CR Circular Level

Special Orders Available

Special order examples

- Change liquid color to transparent
- Chamfering
- Change mounting hole diameter

The following option fees may be quoted separately.

Sensitivity 0.5mm/m = 0.0286° *CR-15,CR-20 : Sensitivity 1.3mm/m = 0.0764°

CR-35



Circular Level

Product No.	Size	Vial Size	Scale Width	Weight	Quantity per Carton	Retail Price	JAN Code
CR-15	φ15×10mm	φ5×10mm	6mm	2g	1	1,200yen	4 993711 581318
CR-20	φ20×15mm	φ6×12mm	6mm	5.5g	1	1,220yen	4 993711 581325
CR-25	φ25×15mm	φ8×15mm	8mm	8.5g	1	1,330yen	4 993711 581332
CR-30	φ30×15mm	φ8×20mm	11mm	12.5g	1	1,380yen	4 993711 581349
CR-35	φ35×15mm	φ8×25mm	13mm	16.5g	1	1,460yen	4 993711 581356

CRT 2 Way Circular Level

Special Orders Available

Sensitivity 1.3mm/m = 0.0764° *CRT-60 : Sensitivity 0.5mm/m = 0.0286°

CRT-35



2 Way Circular Level

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
CRT-25	φ25×10mm	φ6×10mm	6mm	6g	1	1,610yen	4 993711 581615
CRT-30	φ30×10mm	φ6×13mm	7mm	8g	1	1,660yen	4 993711 581622
CRT-35	φ35×12mm	φ7×17mm	8mm	14g	1	1,720yen	4 993711 581639
CRT-60	φ60×14mm	φ8×25mm	13mm	48g	1	5,720yen	4 993711 581646

CRTh 2 Way Circular Level (With Mounting Holes)

Special Orders Available

Sensitivity 1.3mm/m = 0.0764° *CRTh-60 : Sensitivity 0.5mm/m = 0.0286°

CRTh-35



2 Way Circular Level (With Mounting Holes)

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Hope Pitch	Hole Diameter (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
CRTh-25	φ25×10mm	φ6×10mm	6mm	16mm	2.7mm	5g	1	1,740yen	4 993711 582414
CRTh-30	φ30×10mm	φ6×13mm	7mm	20mm	2.7mm	7g	1	1,790yen	4 993711 582421
CRTh-35	φ35×12mm	φ7×17mm	8mm	23mm	2.7mm	13g	1	1,870yen	4 993711 582438
CRTh-60	φ60×14mm	φ8×25mm	13mm	40mm	4.2mm	47g	1	5,880yen	4 993711 582445

Oh Oval Level (With Mounting Holes)

Special Orders Available

Sensitivity 0.5mm/m = 0.0286° *Oh-25,Oh-30 : Sensitivity 1.3mm/m = 0.0764°

Oh-50



Oval Level (With Mounting Holes)

Product No.	Size	Vial Size	Scale Width	Hope Pitch	Hole Diameter (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
Oh-25	8×8×25mm	φ5×10mm	6mm	18mm	2.2mm	2g	1	1,460yen	4 993711 582117
Oh-30	10×10×30mm	φ6×12mm	7mm	22mm	2.2mm	3g	1	1,460yen	4 993711 582124
Oh-40	13×13×40mm	φ8×17mm	10mm	27mm	3.2mm	7g	1	1,530yen	4 993711 582131
Oh-50	15×15×50mm	φ8×23mm	13mm	35mm	3.2mm	11g	1	1,640yen	4 993711 582148
Oh-60	15×15×60mm	φ8×25mm	13mm	45mm	3.2mm	14g	1	1,720yen	4 993711 582155
Oh-70	15×15×70mm	φ8×25mm	13mm	55mm	3.2mm	16g	1	1,790yen	4 993711 582162

OTH 2 Way Oval Level (With Mounting Holes)

Special Orders Available

Sensitivity 0.5mm/m = 0.0286° *OTH-50 : Sensitivity 1.3mm/m = 0.0764°

OTH-50



2 Way Oval Level (With Mounting Holes)

Product No.	Size	Vial Size (2 points)	Scale Width (2 points)	Hope Pitch	Hole Diameter (2 points)	Weight	Quantity per Carton	Retail Price	JAN Code
OTH-50	20×50×10mm	φ6×13mm	6mm	40mm	2.7mm	10g	1	2,570yen	4 993711 582544
OTH-64	24×64×13mm	φ6×17mm	8mm	52mm	3.2mm	20g	1	2,860yen	4 993711 582551
OTH-84	34×84×15mm	φ8×25mm	13mm	67mm	3.2mm	45g	1	3,150yen	4 993711 582568