


ルーマドリル ショート刃

Micro Drill Short Flute Length

ADRS



■ 精密・多孔細穴加工用ドリルです。

Best for drilling precision small holes.

■ 一般鋼材から非鉄、樹脂まで幅広い適用が可能です。

Wide application available covering from steel to non-ferrous and resin.

刃径公差：+0~-0.005

φD Tolerance

型番 CODE NUMBER	径 φD	刃長 ℓ	全長 L	シャンク d	定価 ¥
ADRS-0010	0.1	0.6	38	3	5,400
ADRS-0011	0.11	0.6	38	3	5,400
ADRS-0012	0.12	0.6	38	3	5,400
ADRS-0013	0.13	0.6	38	3	5,400
ADRS-0014	0.14	0.6	38	3	5,400
ADRS-0015	0.15	0.8	38	3	5,400
ADRS-0016	0.16	0.8	38	3	5,400
ADRS-0017	0.17	0.8	38	3	5,400
ADRS-0018	0.18	1.0	38	3	4,900
ADRS-0019	0.19	1.0	38	3	4,900
ADRS-0020	0.2	1.0	38	3	4,900
ADRS-0021	0.21	1.0	38	3	4,440
ADRS-0022	0.22	1.2	38	3	4,440
ADRS-0023	0.23	1.2	38	3	4,440
ADRS-0024	0.24	1.2	38	3	4,440
ADRS-0025	0.25	1.5	38	3	4,440
ADRS-0026	0.26	1.5	38	3	4,440
ADRS-0027	0.27	1.5	38	3	4,440
ADRS-0028	0.28	1.5	38	3	4,440
ADRS-0029	0.29	1.5	38	3	4,440
ADRS-0030	0.3	2.5	38	3	4,440
ADRS-0031	0.31	2.5	38	3	3,340
ADRS-0032	0.32	2.5	38	3	3,340
ADRS-0033	0.33	2.5	38	3	3,340
ADRS-0034	0.34	2.5	38	3	3,340
ADRS-0035	0.35	2.5	38	3	3,340



型番 CODE NUMBER	径 φD	刃長 ℓ	全長 L	シャンク d	定価 ¥
ADRS-0036	0.36	2.5	38	3	3,340
ADRS-0037	0.37	2.5	38	3	3,340
ADRS-0038	0.38	2.5	38	3	3,340
ADRS-0039	0.39	2.5	38	3	3,340
ADRS-0040	0.4	3	38	3	3,340
ADRS-0041	0.41	3	38	3	3,340
ADRS-0042	0.42	3	38	3	3,340
ADRS-0043	0.43	3	38	3	3,340
ADRS-0044	0.44	3	38	3	3,340
ADRS-0045	0.45	3	38	3	3,340
ADRS-0046	0.46	3	38	3	3,340
ADRS-0047	0.47	3	38	3	3,340
ADRS-0048	0.48	3	38	3	3,340
ADRS-0049	0.49	3	38	3	3,340
ADRS-0050	0.5	3	38	3	3,340
ADRS-0051	0.51	3	38	3	3,340
ADRS-0052	0.52	3	38	3	3,340
ADRS-0053	0.53	3	38	3	3,340
ADRS-0054	0.54	3	38	3	3,340
ADRS-0055	0.55	3	38	3	3,340
ADRS-0056	0.56	3	38	3	3,340
ADRS-0057	0.57	3	38	3	3,340
ADRS-0058	0.58	3	38	3	3,340
ADRS-0059	0.59	3	38	3	3,340
ADRS-0060	0.6	3	38	3	3,340
ADRS-0061	0.61	3	38	3	3,340