

HexPro™ Pivot Head Wrenches

- Chrome Finish -

L-Wrenches

Sets	PART#	MODEL#	PCS	PACKED IN	CARD	POUCH	CONTENTS	QTY	LIST
Inch Hex	00009	HP5-IC-09	5	Box		✓	3/16, 7/32, 1/4, 5/16, 3/8"	1	
	00017	HP8-IC-17	8	Box		✓	1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	
	00047	HP5-IC-47R	5	Transparent Clamshell	*ROY	✓	9/64, 5/32, 3/16, 1/4, 5/16"	1	
	00038	HP5-IC-38R	5	Bondhex™ Case/Clamshell	*ROY		3/16, 7/32, 1/4, 5/16, 3/8"	1	
	00033	HP5-IC-33R	5	Bondhex™ Case/Clamshell	*ROY		1/8, 5/32, 3/16, 1/4, 5/16"	1	
	00060	HP5-IC-60B	5	Transparent Clamshell	Blue		3/16, 7/32, 1/4, 5/16, 3/8"	1	
	00068	HP5-IC-68B	5	Transparent Clamshell	Blue	✓	3/16, 7/32, 1/4, 5/16, 3/8"	1	
Metric Hex	00005	HP5-IC-05	5	Box		✓	4, 5, 6, 8, 10mm	1	
	00010	HP6-IC-10	6	Box		✓	3, 4, 5, 6, 8, 10mm	1	
	00062	HP5-IC-62R	5	Transparent Clamshell	*ROY		3, 4, 5, 6, 8mm	1	
	00064	HP5-IC-64R	5	Transparent Clamshell	*ROY	✓	3, 4, 5, 6, 8mm	1	
	00051	HP5-IC-51R	5	Transparent Clamshell	*ROY		4, 5, 6, 8, 10mm	1	
	00053	HP5-IC-53R	5	Transparent Clamshell	*ROY	✓	4, 5, 6, 8, 10mm	1	
	00069	HP5-IC-69B	5	Transparent Clamshell	Blue	✓	3, 4, 5, 6, 8 mm	1	
	00070	HP5-IC-70B	5	Transparent Clamshell	Blue		4, 5, 6, 8, 10mm	1	
	00073	HP5-IC-73B	5	Transparent Clamshell	Blue	✓	4, 5, 6, 8, 10mm	1	
	00025	HP5-IC-25R	5	Bondhex™ Case/Clamshell	*ROY		3, 4, 5, 6, 8 mm	1	
00035	HP6-IC-35R	6	Bondhex™ Case/Clamshell	*ROY		4, 5, 6, 7, 8, 10mm	1		
TORX®	00019	SP5-IC-19	5	Box		✓	T15, T20, T25, T27, T30	1	
	00018	SP5-IC-18	5	Box		✓	T40, T45, T47, T50, T55	1	
	00015	SP6-IC-15	6	Box		✓	T25, T27, T30, T40, T45, T50	1	
	00022	SP10-IC-22	10	Box		✓	T15, T20, T25, T27, T30, T40, T45, T47, T50, T55	1	
	00055	SP5-IC-55R	5	Transparent Clamshell	*ROY		T25, T30, T40, T45, T50	1	
	00077	SP5-IC-77R	5	Transparent Clamshell	*ROY		T20, T25, T30, T40, T50	1	
	00075	SP5-IC-75B	5	Transparent Clamshell	Blue		T25, T30, T40, T45, T50	1	
	00078	SP5-IC-78B	5	Transparent Clamshell	Blue	✓	T25, T30, T40, T45, T50	1	
	00079	SP5-IC-79B	5	Transparent Clamshell	Blue	✓	T25, T27, T30, T40, T50	1	
	00080	SP5-IC-80B	5	Transparent Clamshell	Blue		T20, T25, T30, T40, T45	1	
	00023	SP5-IC-23R	5	Bondhex™ Case/Clamshell	*ROY		T20, T25, T30, T40, T45	1	
	00039	SP5-IC-39R	5	Bondhex™ Case/Clamshell	*ROY		T30, T40, T45, T47, T50	1	

*ROY - red, orange & yellow card

	SIZES					PACKAGED			TAGGED/BARCODED			
	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST EA	PART#	QTY	LIST EA	
Inch	1/8	3.8	97	1.10	28	88007	1		88707	1		
	9/64	3.8	97	1.10	28	88008	1		88708	1		
	5/32	4.2	108	1.20	31	88009	1		88709	1		
	3/16	4.6	118	1.30	33	88010	1		88710	1		
	7/32	5.0	128	1.40	36	88011	1		88711	1		
	1/4	5.4	138	1.60	41	88012	1		88712	1		
	5/16	6.4	163	1.90	48	88013	1		88713	1		
3/8	7.0	177	2.00	51	88014	1		88714	1			
Metric	3	3.8	97	1.10	28	88056	1		88756	1		
	4	4.2	108	1.20	31	88060	1		88760	1		
	5	4.6	118	1.30	33	88064	1		88764	1		
	6	5.4	138	1.60	41	88068	1		88768	1		
	7	6.4	163	1.90	48	88070	1		88770	1		
	8	6.4	163	1.90	48	88072	1		88772	1		
10	7.0	177	2.00	51	88076	1		88776	1			
Singles	TORX®	T15	4.2	108	1.20	31	88215	1		88715	1	
		T20	4.2	108	1.20	31	88220	1		88720	1	
		T25	4.6	118	1.30	33	88225	1		88725	1	
		T27	4.6	118	1.30	33	88227	1		88727	1	
		T30	4.6	118	1.30	33	88230	1		88730	1	
		T40	5.4	138	1.60	41	88240	1		88740	1	
		T45	6.4	163	1.90	48	88245	1		88745	1	
		T47	6.4	163	1.90	48	88247	1		88747	1	
		T50	6.4	163	1.90	48	88250	1		88750	1	
		T55	7.0	177	2.00	51	88255	1		88755	1	

