


FERRULE REDUCER (CONCENTRIC · ECCENTRIC)

Material 304/316L



SIZE	L	SIZE	L
1.25S×1S	109	3S×2.5S	109
1.5S×1.25S	109	3S×2S	109
1.5S×1S	109	3S×1.5S	109
2S×1.5S	109	3.5S×3S	109
2S×1.25S	109	3.5S×2.5S	109
2S×1S	109	3.5S×2S	109
2.5S×2S	109	4S×3.5S	144
2.5S×1.5S	109	4S×3S	144
2.5S×1.25S	109	4S×2.5S	144
2.5S×1S	109	4S×2S	144

FERRULE CROSS

Material 304/316L



One side, two sides and three sides are available

SIZE	A
1S	55
1.25S	55
1.5S	70
2S	82
2.5S	105
3S	110
3.5S	125
4S	154.4

180° BEND BOTH END FERRULE

Material 304/316L



One side is available

SIZE	A	B
1.5S	152.4	97.2
2S	152.4	97.2
2.5S	190.6	116.3
3S	254.0	148.0
4S	254.0	148.0

FERRULE HOSE ADAPTOR

Material 304/316L



Reduced type is available

SIZE	D	L
1S	25.4	81
1.25S	31.8	※
1.5S	38.1	101
2S	50.8	101
2.5S	63.5	101
3S	76.3	101
3.5S	89.1	※
4S	101.6	※

FERRULE (SCREW·NUT) FLANGE ADAPTOR

Material 304/316L



JIS 5K or other size are available

SIZE	d	L	D
1S×10k-20A	23.0	54	100
1S×10k-25A	23.0	54	125
1.5S×10k-32A	35.7	56	135
1.5S×10k-40A	35.7	56	140
2S×10k-40A	47.8	56	140
2S×10k-50A	47.8	56	155
2.5S×10k-50A	59.5	56	155
2.5S×10k-65A	59.5	58	175
3S×10k-65A	72.3	58	175
3S×10k-80A	72.3	58	185
4S×10k-80A	97.6	58	185

SANITARY FITTINGS UNION PARTS

MALE FOR WELD

Material 304/316L



SIZE	D	C	L
1S	25.4	23.0	21
1.25S	31.8	29.4	※
1.5S	38.1	35.7	21
2S	50.8	47.8	21
2.5S	63.5	59.5	21
3S	76.3	72.3	21
3.5S	89.1	85.1	※
4S	101.6	97.6	27.5

LONG MALE FOR WELD

Material 304/316L



SIZE	D	C	L
1S	25.4	23.0	42
1.25S	31.8	29.4	※
1.5S	38.1	35.7	42
2S	50.8	47.8	42
2.5S	63.5	59.5	42
3S	76.3	72.3	42
3.5S	89.1	85.1	※
4S	101.6	97.6	42

LINER FOR WELD

Material 304/316L



SIZE	D	C	L
1S	25.4	23.0	21
1.25S	31.8	29.4	※
1.5S	38.1	35.7	21
2S	50.8	47.8	21
2.5S	63.5	59.5	21
3S	76.3	72.3	21
3.5S	89.1	85.1	※
4S	101.6	97.6	27.5

LONG LINER FOR WELD

Material 304/316L



SIZE	D	C	L
1S	25.4	23.0	42
1.25S	31.8	29.4	※
1.5S	38.1	35.7	42
2S	50.8	47.8	42
2.5S	63.5	59.5	42
3S	76.3	72.3	42
3.5S	89.1	85.1	※
4S	101.6	97.6	42