


# タッチコネクタファイブ ミニスピードコントローラ

## TOUCH CONNECTOR FIVE MINI SPEED CONTROLLER

### タッチコネクタファイブ ミニスピードコントローラ $\alpha$




型式 Model		A	B1	B2	$\phi C$	適用 チューブ 外径 Tube O. D. $\phi D$	E	二面幅 Spanner Flats H	L	ねじサイズ Thread T (おねじ)	チューブ 挿入寸法 Tube Insertion Depth	重量 Weight (g)
本体色黒 Black body	本体色白 White body											
FM4R-M3-0(I)	FM4R-M3W-0(I)	19.9	30.1	32.5	11.0	4	13.0	8.0	10.5	M3×0.5	12.0	11.0
FM4R-M5-0(I)	FM4R-M5W-0(I)	19.9	31.1	33.5	11.0	4	14.0	8.0	10.5	M5×0.8	12.0	12.0
FM4R-01-0(I)	FM4R-01W-0(I)	19.9	33.6	36.0	11.0	4	16.5	10.0	12.5	R1/8	12.0	15.0
FM6R-M5-0(I)	FM6R-M5W-0(I)	22.3	31.1	33.5	13.0	6	15.0	8.0	11.5	M5×0.8	12.5	13.5
FM6R-01-0(I)	FM6R-01W-0(I)	22.3	33.6	36.0	13.0	6	17.5	10.0	13.5	R1/8	12.5	16.5



### タッチコネクタファイブ ミニスピードコントローラ $\beta$



型式 Model		A	B1	B2	$\phi C$	適用 チューブ 外径 Tube O. D. $\phi D$	E	二面幅 Spanner Flats H	L	P	R	ねじサイズ Thread T (おねじ)	チューブ 挿入寸法 Tube Insertion Depth	重量 Weight (g)
本体色黒 Black body	本体色白 White body													
FMB4R-M3-0(I)	FMB4R-M3W-0(I)	19.9	30.1	32.5	11.0	4	12.5	8.0	10.0	11.3	17.9	M3×0.5	12.0	12.5
FMB4R-M5-0(I)	FMB4R-M5W-0(I)	19.9	31.1	33.5	11.0	4	13.5	8.0	10.0	11.3	17.9	M5×0.8	12.0	13.5
FMB4R-01-0(I)	FMB4R-01W-0(I)	19.9	33.6	36.0	11.0	4	16.0	10.0	12.0	11.3	17.9	R1/8	12.0	16.5
FMB6R-M5-0(I)	FMB6R-M5W-0(I)	22.3	31.1	33.5	13.0	6	13.5	8.0	10.0	12.3	17.9	M5×0.8	12.5	15.0
FMB6R-01-0(I)	FMB6R-01W-0(I)	22.3	33.6	36.0	13.0	6	16.0	10.0	12.0	12.3	17.9	R1/8	12.5	18.0



\*上記に表示されていない単位は全てmm