

## TLS-6 / TLS-7 / TLS-7S / TLS-8 / TLS-9

## FLAT TYPE HOLDER SET (mm. size)

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Slide blister pack

Item No.	Pcs.	H								Inner	D×W×H	g	
TLS-6	6	1.5	2	2.5	3	4	5		10	235×150×53	973		
TLS-7	7	2.5	3	4	5	6	8	10	5	311×120×68	2,316		
TLS-7S	7	1.5	2	2.5	3	4	5	6	10	256×160×53	1,535		
TLS-8	8	1.5	2	2.5	3	4	5	6	8	5	290×103×55	1,359	
TLS-9	9	1.5	2	2.5	3	4	5	6	8	10	5	311×120×68	2,343



TLS-9



TLS-8



TLS-7S



TLS-6


## TL- \* / TEL- \*

## INDIVIDUAL (mm. size / inch size)

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Bulk pack



TL-6



Item No.	H	L1	L2	Inner	D×W×H	g
TL-1.5	1.5	16	79	20	162×68×35	50
TL-2	2	17	95	20	162×68×35	90
TL-2.5	2.5	18	110	20	162×68×35	130
TL-3	3	20	126	20	162×68×35	210
TL-4	4	25	142	20	162×68×35	390
TL-5	5	28	160	20	202×65×32	660
TL-6	6	32	180	20	226×75×32	1,055
TL-8	8	36	200	10	226×75×32	1,376
TL-10	10	40	224	10	250×90×38	2,136
TL-11	11 (7/16")	43	240	4	275×78×35	995
TL-12	12	45	250	4	275×78×35	1,190
TL-14	14	55	280	4	302×90×35	1,815
TL-17	17	60	320	4	347×102×43	3,025
TL-19	19 (3/4")	70	360	4	411×96×47	4,255

※Pack packaging is also available except for TL-17 to TL-19.

Item No.	H	L1	L2	Inner	D×W×H	g
TEL-1/16	1/16"	15	79	20	162×68×35	55
TEL-5/64	5/64"	17	93	20	162×68×35	90
TEL-3/32	3/32"	18	108	20	126×65×32	120
TEL-1/8	1/8"	20	127	20	162×68×35	220
TEL-5/32	5/32"	25	140	20	162×68×35	380
TEL-3/16	3/16"	28	158	20	202×65×32	600
TEL-1/4	1/4"	32	178	20	226×75×32	1,200
TEL-5/16	5/16"	36	198	10	226×75×32	1,025
TEL-3/8	3/8"	40	222	10	226×75×32	1,625
TL-7/16	7/16"	43	240	4	275×78×35	995
TL-1/2	1/2"	45	248	4	275×78×35	1,320
TL-9/16	9/16"	55	278	4	302×90×35	995
TL-5/8	5/8" (16mm)	60	320	4	347×102×43	2,645
TL-3/4	3/4"	70	360	4	411×96×47	4,255

※Please note Item No. changes (TEL / TL) depending on sizes.

※Pack packaging is also available except for TL-9/16 to TL-3/4.