

016-158D / 016-1510D / 016-13ZD / 016-S412

DOOR HOLDER SET (mm. size / inch size)

SURFACE TREATMENT : Black parkerized finish / PACKAGE : Slide blister pack

EXCELLENT

STANDARD

TORX®

TORX®



016-1510D



016-S412

NEW

Ball Point designed to be a regular sphere that contacts cap bolt walls evenly to prevent from wearing out. Metric 8pcs., 9pcs., and Inch size 13 pcs. set comes with door type holders.



016-13ZD




Item No.	Pcs.		H								Inner	D×W×H	g
016-158D	8	1.5	2	2.5	3	4	5	6	8	5	232×93×105	1,256	
016-1510D	9	1.5	2	2.5	3	4	5	6	8	10	5	257×103×126	2,097
016-13ZD	13	0.05" 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8								5	210×144×85	2,418	
016-S412	6	4	5	6	8	10	12				5	311×120×60	3,190

016-*

INDIVIDUAL (mm. size / inch size)

SURFACE TREATMENT : Black parkerized finish / PACKAGE : Bulk pack



016-6mm

Item No.	H	L1	L2	Inner	D×W×H	g
016-1.27mm	1.27 (0.05")	14	75	50	95×75×50	74
016-1.5mm	1.5	16	79	50	95×75×50	104
016-2mm	2	17	86	50	95×75×50	170
016-2.5mm	2.5	18	94	50	110×80×47	267
016-3mm	3	20	101	50	110×80×47	399
016-4mm	4	25	110	50	136×90×53	770
016-5mm	5	28	120	50	136×90×53	1,286
016-5.5mm	5.5	30	127	50	182×94×52	1,661
016-6mm	6	32	133	50	182×94×52	2,037
016-8mm	8	36	154	25	182×94×52	2,097
016-10mm	10	40	172	25	198×110×63	3,626
016-12mm	12	45	206	10	302×90×35	2,491
016-14mm	14	55	225	6	302×90×35	2,297
016-17mm	17	60	250	4	347×102×43	2,510
016-19mm	19 (3/4")	70	280	4	347×102×43	3,505
016-22mm	22	85	325	—	—	—

※Pack packaging is also available except for 016-12mm to 016-22mm.

Item No.	H	L1	L2	Inner	D×W×H	g
016-0.05"	0.05" (1.27mm)	14	75	50	95×75×50	74
016-1/16"	1/16"	15	79	50	95×75×50	104
016-5/64"	5/64"	17	84	50	95×75×50	154
016-3/32"	3/32"	17	92	50	110×80×47	245
016-7/64"	7/64"	19	97	50	110×80×47	333
016-1/8"	1/8"	20	102	50	110×80×47	446
016-9/64"	9/64"	23	104	50	110×80×47	577
016-5/32"	5/32"	25	108	50	136×90×53	744
016-3/16"	3/16"	28	118	50	136×90×53	1,148
016-7/32"	7/32"	30	125	50	182×94×52	1,653
016-1/4"	1/4"	32	135	50	182×94×52	2,300
016-5/16"	5/16"	36	152	25	182×94×52	2,028
016-3/8"	3/8"	40	170	25	198×110×63	3,268

※Pack packaging is also available.

