

## 018-S1 / 018-S2

SET (mm. size / inch size)

SURFACE TREATMENT : Nickel plated finish blade / PACKAGE : Slide blister pack



018-S1



018-S2

Item No.	Pcs.	H					Inner	D×W×H	g
018-S1	5	2.5	3	4	5	6	5	340×240×95	2,057
018-S2	5	3/32	1/8	5/32	3/16	1/4	5	340×240×95	2,069

## 018- \* H

INDIVIDUAL (mm. size / inch size)

SURFACE TREATMENT : Nickel plated finish blade / PACKAGE : Bulk pack



Printed header for hanging display.

Item No.	H	L1	L2	L3	Inner	D×W×H	g
018-2	2	85	71	110	10	140×105×55	282
018-2.5	2.5	85	110	150	10	187×90×70	335
018-3	3	85	126	167	10	200×91×70	373
018-4	4	100	130	180	10	220×106×76	598
018-5	5	100	153	203	10	245×106×76	749
018-6	6	125	173	233	10	284×130×85	1,280
018-8	8	200	184	264	10	305×205×90	2,753
018-10	10	200	204	284	10	336×212×90	3,479

※Paper hanger packaging is also available.

Item No.	H	L1	L2	L3	Inner	D×W×H	g
018-5/64	5/64"	85	71	110	10	140×105×55	282
018-3/32	3/32"	85	110	150	10	187×90×70	326
018-1/8	1/8"	85	128	168	10	200×91×70	387
018-5/32	5/32"	100	130	180	10	220×106×76	595
018-3/16	3/16"	100	153	203	10	245×106×76	708
018-7/32	7/32"	125	160	220	10	284×130×85	1,170
018-1/4	1/4"	125	173	233	10	284×130×85	1,344

※Paper hanger packaging is also available.



Please be sure to read "Attention on use" in the appendix.

EXCELLENT

STANDARD

TORX®

IOR&Co., Ltd.

L TYPE

KNIFE TYPE

SCREW DRIVER TYPE

T-HANDLE TYPE

SOCKET BIT TYPE

BIT TYPE