

Poly Chain® GT® Carbon™ Belts

Product No. Series 9274 (continued)

8mm Pitch — 62mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
8MGT-1792-62	9274-3224	224	70.55	2.10
8MGT-2000-62	9274-3250	250	78.74	2.30
8MGT-2200-62	9274-3275	275	86.61	2.50
8MGT-2240-62	9274-3280	280	88.19	2.55
8MGT-2400-62	9274-3300	300	94.49	2.80
8MGT-2520-62	9274-3315	315	99.21	2.90
8MGT-2600-62	9274-3325	325	102.36	2.95
8MGT-2800-62	9274-3350	350	110.24	3.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
8MGT-2840-62	9274-3355	355	111.81	3.15
8MGT-3048-62	9274-3381	381	120.00	3.40
8MGT-3200-62	9274-3400	400	125.98	3.60
8MGT-3280-62	9274-3410	410	129.13	3.70
8MGT-3600-62	9274-3450	450	141.73	4.05
8MGT-4000-62	9274-3500	500	157.48	4.40
8MGT-4400-62	9274-3550	550	173.23	4.80
8MGT-4480-62	9274-3560	560	176.38	4.90

14mm Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-994-20	9274-4071	71	39.13	1.30
14MGT-1120-20	9274-4080	80	44.09	1.35
14MGT-1190-20	9274-4085	85	46.85	1.40
14MGT-1260-20	9274-4090	90	49.61	1.45
14MGT-1400-20	9274-4100	100	55.12	1.55
14MGT-1568-20	9274-4112	112	61.73	1.65
14MGT-1610-20	9274-4115	115	63.39	1.70
14MGT-1750-20	9274-4125	125	68.90	1.75
14MGT-1890-20	9274-4135	135	74.41	1.75
14MGT-1960-20	9274-4140	140	77.17	1.80
14MGT-2100-20	9274-4150	150	82.68	1.90
14MGT-2240-20	9274-4160	160	88.19	1.98
14MGT-2310-20	9274-4165	165	90.95	2.05
14MGT-2380-20	9274-4170	170	93.70	2.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-2450-20	9274-4175	175	96.46	2.15
14MGT-2520-20	9274-4180	180	99.21	2.20
14MGT-2590-20	9274-4185	185	101.97	2.20
14MGT-2660-20	9274-4190	190	104.72	2.25
14MGT-2800-20	9274-4200	200	110.24	2.30
14MGT-3136-20	9274-4224	224	123.46	2.50
14MGT-3304-20	9274-4236	236	130.08	2.55
14MGT-3360-20	9274-4240	240	132.28	2.60
14MGT-3500-20	9274-4250	250	137.80	2.70
14MGT-3850-20	9274-4275	275	151.58	2.85
14MGT-3920-20	9274-4280	280	154.33	2.95
14MGT-4326-20	9274-4309	309	170.32	3.15
14MGT-4410-20	9274-4315	315	173.62	3.20

14mm Pitch — 37mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-994-37	9274-5071	71	39.13	1.60
14MGT-1120-37	9274-5080	80	44.09	1.70
14MGT-1190-37	9274-5085	85	46.85	1.75
14MGT-1260-37	9274-5090	90	49.61	1.80
14MGT-1400-37	9274-5100	100	55.12	2.05
14MGT-1568-37	9274-5112	112	61.73	2.20
14MGT-1610-37	9274-5115	115	63.39	2.30
14MGT-1750-37	9274-5125	125	68.90	2.45
14MGT-1890-37	9274-5135	135	74.41	2.55
14MGT-1960-37	9274-5140	140	77.17	2.60
14MGT-2100-37	9274-5150	150	82.68	2.70
14MGT-2240-37	9274-5160	160	88.19	2.85
14MGT-2310-37	9274-5165	165	90.95	2.90
14MGT-2380-37	9274-5170	170	93.70	3.00

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-2450-37	9274-5175	175	96.46	3.10
14MGT-2520-37	9274-5180	180	99.21	3.20
14MGT-2590-37	9274-5185	185	101.97	3.25
14MGT-2660-37	9274-5190	190	104.72	3.35
14MGT-2800-37	9274-5200	200	110.24	3.40
14MGT-3136-37	9274-5224	224	123.46	3.65
14MGT-3304-37	9274-5236	236	130.08	3.85
14MGT-3360-37	9274-5240	240	132.28	3.85
14MGT-3500-37	9274-5250	250	137.80	3.95
14MGT-3850-37	9274-5275	275	151.58	4.25
14MGT-3920-37	9274-5280	280	154.33	4.35
14MGT-4326-37	9274-5309	309	170.32	4.70
14MGT-4410-37	9274-5315	315	173.62	4.75

14mm Pitch — 68mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-994-68	9274-6071	71	39.13	2.40
14MGT-1120-68	9274-6080	80	44.09	2.60
14MGT-1190-68	9274-6085	85	46.85	2.70
14MGT-1260-68	9274-6090	90	49.61	2.80
14MGT-1400-68	9274-6100	100	55.12	3.00
14MGT-1568-68	9274-6112	112	61.73	3.25
14MGT-1610-68	9274-6115	115	63.39	3.40
14MGT-1750-68	9274-6125	125	68.90	3.60
14MGT-1890-68	9274-6135	135	74.41	3.95

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
14MGT-1960-68	9274-6140	140	77.17	4.00
14MGT-2100-68	9274-6150	150	82.68	4.20
14MGT-2240-68	9274-6160	160	88.19	4.50
14MGT-2310-68	9274-6165	165	90.95	4.70
14MGT-2380-68	9274-6170	170	93.70	4.70
14MGT-2450-68	9274-6175	175	96.46	4.85
14MGT-2520-68	9274-6180	180	99.21	4.90
14MGT-2590-68	9274-6185	185	101.97	5.00
14MGT-2660-68	9274-6190	190	104.72	5.15