



Cable ties for outdoor use (UV-resistant)

T-Series in PA66W/UV black


These inside serrated cable ties are made of UV-resistant Polyamide 6.6 (PA66W/UV) and thus suitable for outdoor applications. UV stabilised cable ties resist UV radiation for a considerably longer period compared to standard PA66 cable ties. They can easily be used for bundling and securing cables, pipes and hoses especially in outdoor areas.

Features and benefits


- UV-resistant black cable tie available in a wide range of sizes
- Made from 100 % high quality plastic, allows for good recycling
- Inside serration for a strong hold onto bundles
- Easy application either manually or with a processing tool
- Simple to insert due to bent tail



UV-resistant T-Series cable ties (PA66W/UV).



T-Series



T250-series



Material specification please see page 26.



Specific part numbers according to EN45545 available on request.

TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Tools	Article-No.
T18R	2.5	100.0	22.0	80	PA66W	Black (BK)	100 pcs.	2;5-6;25	111-01960
T18I	2.5	145.0	35.0	80	PA66W	Black (BK)	100 pcs.	2;5-6;25	111-02360
T18L	2.5	205.0	50.0	80	PA66W	Black (BK)	100 pcs.	2;5;25	111-02160
T25LL	2.8	330.0	95.0	110	PA66W	Black (BK)	100 pcs.	2;5-6	111-02660
T30R	3.5	150.0	35.0	135	PA66W	Black (BK)	100 pcs.	2;5-6;25	111-03260
T30L	3.5	198.0	50.0	135	PA66W	Black (BK)	100 pcs.	2;5-6;25	111-03460
T30LL	3.5	290.0	80.0	135	PA66W	Black (BK)	100 pcs.	2;5-6;25	111-03570
T40R	4.0	175.0	40.0	180	PA66W	Black (BK)	100 pcs.	2;5-6;8;25	111-01625
T50S	4.6	150.0	35.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05860
T50R	4.6	200.0	50.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-04889
T50M	4.6	245.0	65.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-06206
T50I	4.6	300.0	85.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05260
T50L	4.6	390.0	110.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-05440
T50LL	4.6	445.0	130.0	225	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10;25	111-06000
T80R	4.7	210.0	55.0	355	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10-12;25	111-05060
T80I	4.7	305.0	85.0	355	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10-12;25	111-08290
T80L	4.7	390.0	110.0	355	PA66W	Black (BK)	100 pcs.	2-3;5-6;8;10-12;25	111-05460

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!

www.HT.click/9-42

