

EP-fit	EPCT	Male Connector ANSI NPT ISO/JIS R
--------	------	-----------------------------------



φE (Hose I·D): Refer to Hose dimension sheet on page 46

Part No.		A (Hose O.D)	T	E1	h (HEX)	H (HEX)	φ	φ1	L	(D)	
ANSI NPT	ISO/JIS R	mm	NPT/R	mm	mm	mm	mm	mm	mm	mm	
EPCT 4X□-2 ss	EPCT 4X□-R2 ss	4	1/8	4.0	12	10	27.5	6.0	26.5	1.5	
EPCT 4X□-4 ss	EPCT 4X□-R4 ss	4	1/4	7.0	14	10	31.5	6.0	30.5	1.5	
EPCT 6X□-1 ss	EPCT 6X□-R2 ss EPCT 6X□-R4 ss EPCT 6X□-R6 ss EPCT 6X□-R8 ss	6	1/16	3.0	12	12	26.0	6.5	25.0	2.0	
EPCT 6X□-2 ss		6	1/8	4.0	12	12	28.0	6.5	27.0	2.0	
EPCT 6X□-4 ss		6	1/4	7.0	14	12	32.0	6.5	31.0	2.0	
EPCT 6X□-6 ss		6	3/8	9.0	19	12	33.0	6.5	32.0	2.0	
		6	3/8	9.0	19	12	34.0	6.5	33.0	2.0	
		6	1/2	12.0	22	12	39.0	6.5	38.0	2.0	
EPCT 8X□-2 ss	EPCT 8X□-R2 ss	8	1/8	4.0	14	14	29.5	7.5	28.5	2.0	
EPCT 8X□-4 ss	EPCT 8X□-R4 ss	8	1/4	7.0	14	14	33.5	7.5	32.5	2.0	
EPCT 8X□-6 ss		8	3/8	9.0	19	14	34.5	7.5	33.5	2.0	
		8	3/8	9.0	19	14	35.5	7.5	34.5	2.0	
		8	1/2	12.0	22	14	40.5	7.5	39.5	2.0	
EPCT 10X□-4 ss EPCT 10X□-6 ss	EPCT 10X□-R2 ss	10	1/8	4.0	17	17	30.0	8.0	29.5	2.0	
	EPCT 10X□-R4 ss	10	1/4	7.0	17	17	34.0	8.0	33.5	2.0	
		10	3/8	9.0	19	17	35.0	8.0	34.5	2.0	
		10	3/8	9.0	19	17	36.0	8.0	35.5	2.0	
		10	1/2	12.0	22	17	41.0	8.0	39.5	2.0	
EPCT 12X□-2 ss	EPCT 12X□-R2 ss	12	1/8	4.0	19	19	32.5	9.0	32.0	2.0	
EPCT 12X□-6 ss	EPCT 12X□-R4 ss	12	1/4	7.0	19	19	37.5	9.0	37.0	2.0	
	EPCT 12X□-R6 ss	12	3/8	9.0	19	19	37.5	9.0	37.0	2.0	
EPCT 12X□-8 ss	EPCT 12X□-R8 ss	12	1/2	12.0	22	19	43.5	9.0	43.0	2.0	
EPCT 12X□-12 ss		12	3/4	16.0	27	19	45.5	9.0	45.0	2.0	
	EPCT 12X□-R12 ss	12	3/4	16.0	27	19	46.5	9.0	46.0	2.0	
EPCT 16X□-6 ss EPCT 16X□-8 ss	EPCT 16X□-R4 ss	16	1/4	7.0	22	24	39.0	10.5	37.5	2.5	
		16	3/8	9.0	22	24	39.0	10.5	37.5	2.5	
	EPCT 16X□-R6 ss	16	3/8	9.0	22	24	40.0	10.5	38.5	2.5	
	EPCT 16X□-R8 ss	16	1/2	12.0	22	24	45.0	10.5	43.5	2.5	
	EPCT 16X□-R12 ss	16	3/4	16.0	27	24	49.0	10.5	47.5	2.5	
EPCT 18X□-6 ss EPCT 18X□-8 ss	EPCT 18X□-R4 ss	18	1/4	7.0	24	27	40.5	10.5	39.5	2.0	
		18	3/8	9.0	24	27	40.5	10.5	39.5	2.0	
	EPCT 18X□-R6 ss	18	3/8	9.0	24	27	41.5	10.5	40.5	2.0	
	EPCT 18X□-R8 ss	18	1/2	12.0	24	27	45.5	10.5	44.5	2.0	
		EPCT 18X□-R12 ss	18	3/4	16.0	27	27	49.5	10.5	48.5	2.0
	EPCT 18X□-R16 ss	18	1	22.5	36	27	54.5	10.5	53.5	2.0	
EPCT 19X□-12 ss	EPCT 19X□-R6 ss	19	3/8	9.0	27	27	46.5	11.0	44.5	3.2	
	EPCT 19X□-R8 ss	19	1/2	12.0	27	27	49.5	11.0	47.5	3.2	
		19	3/4	16.0	30	27	49.5	11.0	47.5	3.2	
		EPCT 19X□-R12 ss	19	3/4	16.0	30	27	51.5	11.0	49.5	3.2
		EPCT 19X□-R16 ss	19	1	22.5	36	27	56.5	11.0	54.5	3.2
	EPCT 22X□-R8 ss	22	1/2	12.0	30	32	51.5	12.0	50.0	2.5	
	EPCT 22X□-R12 ss	22	3/4	16.0	30	32	53.5	12.0	52.0	2.5	