



# PUS

## 隔壁ユニオン

### Bulkhead union

ステンレス製

Stainless



| 部品番号<br>PART NO. | 適用チューブ<br>TUBE SIZE<br>TO BE USED<br>外径×内径<br>O.D. (mm)×I.D. (mm) | φd<br>(mm) | L<br>(mm) | 二面幅<br>TWO FACE<br>WIDTH<br>(mm) |                |                | K<br>最大パネル厚<br>MAX. PANEL<br>THICKNESS<br>(mm) | M×P<br>(mm) | 重量<br>WEIGHT<br>(g) |
|------------------|---|------------|-----------|----------------------------------|----------------|----------------|--|-------------|---------------------|
|                  |   |            |           | S <sub>1</sub>                   | S <sub>2</sub> | S <sub>3</sub> |  |             |                     |
| PUS- 6× 4 -SUS   | 6× 4  | 2.9        | 42        | 19                               | 19             | 12             | 8  | 14×1        | —                   |
| PUS- 8× 6 -SUS   | 8× 6  | 4.9        | 47        | 22                               | 22             | 14             | 8  | 16×1.25     | —                   |
| PUS-10× 7.5-SUS  | 10× 7.5   | 6.0        | 55        | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUS-10× 8 -SUS   | 10× 8   | 6.5        | 55        | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUS-12× 9 -SUS   | 12× 9   | 7.5        | 55        | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUS-12×10 -SUS   | 12×10   | 8.5        | 55        | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |



# PUN

## 隔壁オスユニオン

### Bulkhead male union

ステンレス製

Stainless



| 部品番号<br>PART NO.      | 適用チューブ<br>TUBE SIZE<br>TO BE USED<br>外径×内径<br>O.D. (mm)×I.D. (mm) | R   | φd<br>(mm) | L<br>(mm) | 二面幅<br>TWO FACE<br>WIDTH<br>(mm) |                |                | K<br>最大パネル厚<br>MAX. PANEL<br>THICKNESS<br>(mm) | M×P<br>(mm) | 重量<br>WEIGHT<br>(g) |
|-----------------------|---|-----|------------|-----------|----------------------------------|----------------|----------------|--|-------------|---------------------|
|                       |   |     |            |           | S <sub>1</sub>                   | S <sub>2</sub> | S <sub>3</sub> |  |             |                     |
| PUN- 4× 2 -PT1/8-SUS  | 4× 2  | 1/8 | 1.3        | 40.5      | 17                               | 17             | 10             | 8  | 12×1        | —                   |
| PUN- 4× 2 -PT1/4-SUS  | 4× 2  | 1/4 | 1.3        | 43.5      | 17                               | 17             | 10             | 8  | 12×1        | —                   |
| PUN- 4× 2.5-PT1/8-SUS | 4× 2.5  | 1/8 | 1.3        | 40.5      | 17                               | 17             | 10             | 8  | 12×1        | —                   |
| PUN- 4× 2.5-PT1/4-SUS | 4× 2.5  | 1/4 | 1.3        | 43.5      | 17                               | 17             | 10             | 8  | 12×1        | —                   |
| PUN- 6× 4 -PT1/8-SUS  | 6× 4  | 1/8 | 2.9        | 40.5      | 19                               | 19             | 12             | 8  | 14×1        | —                   |
| PUN- 6× 4 -PT1/4-SUS  | 6× 4  | 1/4 | 2.9        | 43.5      | 19                               | 19             | 12             | 8  | 14×1        | —                   |
| PUN- 6× 4 -PT3/8-SUS  | 6× 4  | 3/8 | 2.9        | 43.5      | 19                               | 19             | 12             | 8  | 14×1        | —                   |
| PUN- 8× 6 -PT1/8-SUS  | 8× 6  | 1/8 | 4.9        | 43.5      | 22                               | 22             | 14             | 8  | 16×1.25     | —                   |
| PUN- 8× 6 -PT1/4-SUS  | 8× 6  | 1/4 | 4.9        | 46.5      | 22                               | 22             | 14             | 8  | 16×1.25     | —                   |
| PUN- 8× 6 -PT3/8-SUS  | 8× 6  | 3/8 | 4.9        | 46.5      | 22                               | 22             | 14             | 8  | 16×1.25     | —                   |
| PUN-10× 7.5-PT1/8-SUS | 10× 7.5   | 1/8 | 6.0        | 48.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 7.5-PT1/4-SUS | 10× 7.5   | 1/4 | 6.0        | 51.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 7.5-PT3/8-SUS | 10× 7.5   | 3/8 | 6.0        | 51.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 7.5-PT1/2-SUS | 10× 7.5   | 1/2 | 6.0        | 55.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 8 -PT1/8-SUS  | 10× 8   | 1/8 | 6.5        | 48.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 8 -PT1/4-SUS  | 10× 8   | 1/4 | 6.5        | 51.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 8 -PT3/8-SUS  | 10× 8   | 3/8 | 6.5        | 51.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-10× 8 -PT1/2-SUS  | 10× 8   | 1/2 | 6.5        | 55.5      | 24                               | 24             | 17             | 8  | 18×1.5      | —                   |
| PUN-12× 9 -PT1/4-SUS  | 12× 9   | 1/4 | 7.5        | 51.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUN-12× 9 -PT3/8-SUS  | 12× 9   | 3/8 | 7.5        | 51.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUN-12× 9 -PT1/2-SUS  | 12× 9   | 1/2 | 7.5        | 55.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUN-12×10 -PT1/4-SUS  | 12×10   | 1/4 | 8.5        | 51.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUN-12×10 -PT3/8-SUS  | 12×10   | 3/8 | 8.5        | 51.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |
| PUN-12×10 -PT1/2-SUS  | 12×10   | 1/2 | 8.5        | 55.5      | 27                               | 27             | 19             | 8  | 20×1.5      | —                   |