



TYPE	GLOBE			GLOBE			GLOBE			GLOBE			GLOBE				
Bronze&Brass																	
FIG	C			CA			B			BH			D				
PRESSURE	Class 150			Class 150			Class 150			Class 150			Class 150				
END CONNECTION	BS21 (JIS B0203)			BS21 (JIS B0203)			JIS B2240			JIS B2240			BS21 (JIS B0203)				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	44	66	50	21	66	50	—	—	—	—	—	—	—	—	—
	3/8	10	44	68	50	24	68	50	—	—	—	—	—	—	—	—	—
	1/2	15	53	79	60	28	79	60	83	79	60	83	79	60	64	113	60
	3/4	20	65	93	70	34	93	70	88	94	70	88	94	70	78	138	90
	1	25	77	104	80	40	104	80	100	105	80	100	105	80	90	156	100
	1 1/4	32	85	127	90	47	127	90	113	127	90	113	127	90	105	184	115
	1 1/2	40	100	145	100	52	145	100	120	145	100	120	145	100	120	187	115
	2	50	119	174	115	61	174	115	145	174	115	145	174	115	145	212	135
	2 1/2	65	139	199	135	74	199	135	165	198	135	165	198	135	—	—	—
	3	80	158	215	155	85	215	155	177	215	155	177	215	155	—	—	—
	4	100	—	—	—	—	—	—	220	250	180	220	250	180	—	—	—
BODY	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze				
BONNET	Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze				
STEM	Special Brass			Special Brass			Special Brass			Special Brass			Special Brass				
DISC	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			G/F PTFE				
							Fringed ends undrilled						Soft Seated disc				

TYPE	GLOBE			GLOBE			GLOBE			GLOBE			GLOBE				
Bronze&Brass																	
FIG	DB			DBH			K			J			JB				
PRESSURE	Class 150			Class 150			5K			10K			10K				
END CONNECTION	JIS B2240			JIS B2240			BS21 (JIS B0203)			BS21 (JIS B0203)			JIS B2011				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	—	—	—	—	—	—	—	—	—	50	86	50	—	—	—
	3/8	10	—	—	—	—	—	—	50	87	55	55	87	55	—	—	—
	1/2	15	82	113	60	82	113	60	60	90	60	65	93	60	85	93	60
	3/4	20	95	138	90	95	138	90	70	102	70	80	122	80	95	122	80
	1	25	108	156	100	108	156	100	80	112	80	90	135	90	110	135	90
	1 1/4	32	120	184	115	120	184	115	100	137	90	105	157	100	130	157	100
	1 1/2	40	140	187	115	140	187	115	110	142	100	120	171	115	150	171	115
	2	50	165	212	135	165	212	135	135	173	115	140	196	135	180	196	135
	2 1/2	65	190	244	155	190	244	155	160	203	135	180	232	155	210	232	155
	3	80	220	281	180	220	281	180	190	233	155	200	268	180	240	268	180
	4	100	270	321	225	270	321	225	—	—	—	—	—	—	280	323	225
BODY	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze				
BONNET	Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze			Forged Brass / Cast Bronze				
STEM	Special Brass			Special Brass			Special Brass			Special Brass			Special Brass				
DISC	G/F PTFE			G/F PTFE			Cast Bronze/Cast Bronze			Cast Bronze			Cast Bronze				
	Soft Seated disc Fringed ends undrilled			Soft Seated disc													

Bronze & Brass
 Cast Iron
 Ductile Iron
 Stainless Steel
 Carbon Steel
 Buttery Valve
 Ball Valve
 Ball Valve Seat
 Actuated Valve