



TYPE	A-SERIES GLOBE			A-SERIES GLOBE			B-SERIES LIFT CHECK			B-SERIES SWING CHECK			B-SERIES SWING CHECK				
Stainless Steel																	
FIG	300UPAW			300UPAWM			UN			UO			UOM				
PRESSURE	Class 300			Class 300			10K			10K			10K				
END CONNECTION	ASME B16.5			ASME B16.5			BS21 (JIS B0203)			BS21 (JIS B0203)			BS21 (JIS B0203)				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	3/8	10	—	—	—	—	—	—	55	50	—	—	—	—	—	—	—
	1/2	15	152	184	100	152	184	100	65	53	—	65	45	—	65	45	—
	3/4	20	178	184	100	178	184	100	80	54	—	80	55	—	80	55	—
	1	25	203	185	100	203	185	100	90	62	—	90	61	—	90	61	—
	1 1/4	32	—	—	—	—	—	—	105	66	—	105	71	—	105	71	—
	1 1/2	40	229	234	160	229	234	160	120	76	—	120	72	—	120	72	—
	2	50	267	287	180	267	287	180	140	85	—	140	81	—	140	81	—
	2 1/2	65	292	293	200	292	293	200	—	—	—	180	93	—	180	93	—
3	80	318	402	250	318	402	250	—	—	—	200	104	—	200	104	—	
4	100	356	453	300	356	453	300	—	—	—	—	—	—	—	—	—	
5	125	400	538	350	400	538	350	—	—	—	—	—	—	—	—	—	
6	150	444	606	400	444	606	400	—	—	—	—	—	—	—	—	—	
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
CAP	—			—			Stainless Steel			Stainless Steel			Stainless Steel				
BONNET	Stainless Steel			Stainless Steel			—			—			—				
STEM	Stainless Steel			Stainless Steel			—			—			—				
DISC	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
HINGE PIN	—			—			—			Stainless Steel			Stainless Steel				
	Bellows seal globe valve			Bellows seal globe valve			—			—			—				

TYPE	B-SERIES SWING CHECK			B-SERIES SWING CHECK			A-SERIES LIFT CHECK			A-SERIES LIFT CHECK			A-SERIES LIFT CHECK				
Stainless Steel																	
FIG	UOB			UOBM			10UNA / 10UNAT			10UNAM / 10UNAMT			20UNA / 20UNAT				
PRESSURE	10K			10K			10K			10K			20K				
END CONNECTION	JIS B2220			JIS B2220			JIS B2220			JIS B2220			JIS B2220				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/2	15	85	45	—	85	45	—	108	74	—	108	74	—	152	80	—
	3/4	20	95	55	—	95	55	—	117	76	—	117	76	—	178	78	—
	1	25	110	61	—	110	61	—	127	76	—	127	76	—	203	79	—
	1 1/4	32	130	71	—	130	71	—	140	84	—	140	84	—	—	—	—
	1 1/2	40	150	72	—	150	72	—	165	86	—	165	86	—	229	97	—
	2	50	180	81	—	180	81	—	—	—	—	—	—	—	—	—	—
	2 1/2	65	210	93	—	210	93	—	—	—	—	—	—	—	—	—	—
	3	80	240	104	—	240	104	—	—	—	—	—	—	—	—	—	—
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
CAP	Stainless Steel			Stainless Steel			—			—			—				
COVER	—			—			Stainless Steel			Stainless Steel			Stainless Steel				
DISC	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
HINGE PIN	Stainless Steel			Stainless Steel			—			—			—				
	—			—			Fig. 10UNAT : Gasket / PTFE			Fig. 10UNAMT : Gasket / PTFE			Fig. 20UNAT : Gasket / PTFE				