



TYPE	BALL CHECK			BALL CHECK			B-SERIES Y TYPE STRAINER			B-SERIES Y TYPE STRAINER			B-SERIES Y TYPE STRAINER				
Stainless Steel																	
FIG	10UFT			10UFTE			UY			UYM			UYB				
PRESSURE	10K			10K			20K			20K			10K				
END CONNECTION	JIS B2220			JIS B2220			BS21 (JIS B0203)			BS21 (JIS B0203)			JIS B2220				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	-	-	-	-	-	-	65	50	-	65	50	-	-	-	-
	3/8	10	-	-	-	-	-	-	70	50	-	70	50	-	110	50	-
	1/2	15	-	-	-	-	-	-	85	60	-	85	60	-	120	58	-
	3/4	20	-	-	-	-	-	-	100	65	-	100	65	-	130	66	-
	1	25	-	-	-	-	-	-	115	77	-	115	77	-	150	78	-
	1 1/4	32	-	-	-	-	-	-	135	90	-	135	90	-	170	93	-
	1 1/2	40	190	87	-	-	-	-	150	100	-	150	100	-	190	104	-
	2	50	200	100.5	-	200	97	-	180	115	-	180	115	-	220	122	-
	2 1/2	65	220	123.5	-	220	120.5	-	220	150	-	220	150	-	-	-	-
	3	80	240	150	-	240	146	-	250	193	-	250	193	-	-	-	-
	4	100	290	187	-	290	187	-	-	-	-	-	-	-	-	-	-
	6	150	410	275	-	410	275	-	-	-	-	-	-	-	-	-	-
	8	200	-	-	-	500	366	-	-	-	-	-	-	-	-	-	-
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
COVER	Stainless Steel			Stainless Steel			-			-			-				
CAP	-			-			Stainless Steel			Stainless Steel			Stainless Steel				
DISC	NBR			NBR			-			-			-				
SCREEN	-			-			Stainless Steel			Stainless Steel			Stainless Steel				

TYPE	B-SERIES Y TYPE STRAINER			A-SERIES Y TYPE STRAINER			A-SERIES Y TYPE STRAINER			A-SERIES Y TYPE STRAINER				
Stainless Steel														
FIG	UYBM			10UYA			10UYAM			20UYA				
PRESSURE	10K			10K			10K			20K				
END CONNECTION	JIS B2220			JIS B2220			JIS B2220			JIS B2220				
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D
	3/8	10	110	50	-	-	-	-	-	-	-	-	-	-
	1/2	15	120	58	-	-	-	-	-	-	-	160	70	-
	3/4	20	130	66	-	-	-	-	-	-	-	160	80	-
	1	25	150	78	-	-	-	-	-	-	-	190	92	-
	1 1/4	32	170	93	-	-	-	-	-	-	-	-	-	-
	1 1/2	40	190	104	-	-	-	-	-	-	-	240	125	-
	2	50	220	122	-	-	-	-	-	-	-	250	150	-
	2 1/2	65	-	-	-	270	160	-	270	160	-	300	160	-
	3	80	-	-	-	290	197	-	290	197	-	320	197	-
	4	100	-	-	-	350	233	-	350	233	-	380	246	-
	5	125	-	-	-	390	267	-	390	267	-	-	-	-
	6	150	-	-	-	440	320	-	440	320	-	550	342	-
	8	200	-	-	-	540	380	-	540	380	-	600	430	-
	10	250	-	-	-	760	538	-	760	538	-	760	538	-
	12	300	-	-	-	870	635	-	870	635	-	870	635	-
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				
CAP	Stainless Steel			-			-			-				
COVER	-			Stainless Steel			Stainless Steel			Stainless Steel				
SCREEN	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel				