



TYPE	FLOATING BALL					FLOATING BALL			FLOATING BALL			FLOATING BALL			FLOATING BALL		
Ball Valve																	
FIG	10STLBF					20STLB			UTK			UTKM			UTKW		
PRESSURE	10K					20K			TYPE 600			TYPE 600			TYPE 600		
END CONNECTION	JIS B2239					JIS B2239			BS21 (JIS B0203)			BS21 (JIS B0203)			BS21 (JIS B0203)		
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	-	-	-	-	-	-	39	31	60	39	31	60	39	25	35
	3/8	10	-	-	-	-	-	-	44	36	70	44	36	70	44	29	40
	1/2	15	108	106	130	140	106	130	56.5	41	85	56.5	41	85	56.5	35	55
	3/4	20	117	109	130	152	109	130	59	44	85	59	44	85	59	39	55
	1	25	127	130	160	165	130	160	71	48	100	71	48	100	71	41	69
	1 1/4	32	140	135	160	178	135	160	78	54	100	78	54	100	-	-	-
	1 1/2	40	165	115	230	190	115	230	83	65	125	83	65	125	-	-	-
	2	50	178	120	230	216	120	230	100	72	125	100	72	125	-	-	-
	2 1/2	65	190	153	400	241	153	400	-	-	-	-	-	-	-	-	-
3	80	203	162	400	283	162	400	-	-	-	-	-	-	-	-	-	
4	100	229	199	460	305	241	750	-	-	-	-	-	-	-	-	-	
5	125	356	219	460	-	-	-	-	-	-	-	-	-	-	-	-	
6	150	394	293	1000	403	293	1000	-	-	-	-	-	-	-	-	-	
8	200	457	352	1500	502	352	1500	-	-	-	-	-	-	-	-	-	
BODY	Ductile Iron					Ductile Iron			Stainless Steel			Stainless Steel			Stainless Steel		
CAP	Ductile Iron					Ductile Iron			-			-			-		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
BALL	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
SEAT	PTFE					HYPATITE® PTFE			G/F PTFE			G/F PTFE			G/F PTFE		
	Full Port					Full Port			Reduced Port			Reduced Port			Reduced Port		

TYPE	FLOATING BALL					FLOATING BALL			FLOATING BALL			FLOATING BALL			FLOATING BALL		
Ball Valve																	
FIG	UTKMW					UTFM			UTH			UTHM			UTHL		
PRESSURE	TYPE 600					TYPE 1000			TYPE 800			TYPE 800			TYPE 1000		
END CONNECTION	BS21 (JIS B0203)					BS21 (JIS B0203)			BS21 (JIS B0203)			BS21 (JIS B0203)			BS21 (JIS B0203)		
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/4	8	39	25	35	-	-	-	-	-	-	-	-	-	-	-	-
	3/8	10	44	29	40	-	-	-	-	-	-	-	-	-	-	-	-
	1/2	15	56.5	35	55	62	53	100	60	47	100	60	48	100	60	76	100
	3/4	20	59	39	55	73	63	130	70	53	100	70	54	100	70	80	100
	1	25	71	41	69	85	67	130	80	63	130	80	64	130	80	85	130
	1 1/4	32	-	-	-	98	75	150	95	67	130	95	68	130	95	99	130
	1 1/2	40	-	-	-	108	81	150	108	78	150	108	79	150	108	105	150
	2	50	-	-	-	124	102	200	124	84	150	124	85	150	124	113	150
	BODY	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel	
CAP	-					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
STEM	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
BALL	Stainless Steel					Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel		
SEAT	G/F PTFE					HYPATITE® PTFE			PTFE			PTFE			HYPATITE® PTFE		
	Reduced Port					Full Port			Reduced Port			Reduced Port			Reduced Port		