



TYPE	3WAY FLOATING BALL			3WAY FLOATING BALL			3 PIECE FLOATING BALL			3 PIECE FLOATING BALL			FLOATING BALL					
Ball Valve																		
FIG	UTH4LM			UTH4TM			U3TZM			SWU3TZM			10UT					
PRESSURE	TYPE 800			TYPE 800			TYPE 1000			TYPE 1000			10K					
END CONNECTION	BS21 (JIS B0203)			BS21 (JIS B0203)			BS21 (JIS B0203)			JIS B2316			BS21 (JIS B0203)					
DIMENSIONS	inch	mm		L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	3/8	10	-	-	-	-	-	-	-	-	-	-	-	-	62	71	130	
	1/2	15	69	63	130	69	63	130	63	48	120	63	48	120	65	102	130	
	3/4	20	84	65	130	84	65	130	71	60	130	71	60	130	80	105	130	
	1	25	96	75.5	150	96	75.5	150	90	69	130	90	69	130	90	124	160	
	1 1/4	32	114	79.5	150	114	79.5	150	103	83	150	103	83	150	110	130	160	
	1 1/2	40	132	95.5	230	132	95.5	230	110	88	150	110	88	150	120	115	230	
	2	50	150	101	230	150	101	230	127	104	180	127	104	180	140	120	230	
2 1/2	65	-	-	-	-	-	-	-	-	-	-	-	-	160	155	400		
3	80	-	-	-	-	-	-	-	-	-	-	-	-	182	165	400		
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
CAP	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
STEM	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
BALL	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
SEAT	HYPATITE® PTFE			HYPATITE® PTFE			HYPATITE® PTFE			HYPATITE® PTFE			PTFE					
	Reduced Port			Reduced Port			Reduced Port			Reduced Port Socket Weld End			Full Port					

TYPE	FLOATING BALL			FLOATING BALL			FLOATING BALL			FLOATING BALL			FLOATING BALL					
Ball Valve																		
FIG	10UTB / G-10UTB			10UTDZ / G-10UTDZ			10UTDZM / G-10UTDZM			20UTDZ			20UTDZM					
PRESSURE	10K			10K			10K			20K			20K					
END CONNECTION	JIS B2220			JIS B2220			JIS B2220			JIS B2220			JIS B2220					
DIMENSIONS	inch	mm		L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/2	15	110	102	130	108	108	130	108	108	130	140	108	130	140	108	130	
	3/4	20	120	105	130	117	111	130	117	111	130	152	111	130	152	111	130	
	1	25	130	124	160	127	124	160	127	124	160	165	124	160	165	124	160	
	1 1/4	32	140	128	160	140	128	160	140	128	160	178	128	160	178	128	160	
	1 1/2	40	165	115	230	165	134	230	165	134	230	190	134	230	190	134	230	
	2	50	180	120	230	178	143	230	178	143	230	216	143	230	216	143	230	
	2 1/2	65	190	155	400	190	179	400	190	179	400	241	179	400	241	179	400	
	3	80	200	165	400	203	189	400	203	189	400	283	189	400	283	189	400	
	4	100	230	200	460	229	224	460	229	224	460	305	251	750	305	251	750	
	5	125	300	220	460	356	240	460	356	240	460	381	267	750	381	267	750	
6	150	340	295	1000	394	315	1000	394	315	1000	403	315	1000	403	315	1000		
8	200	450	355	1500	457	406	1500	457	406	1500	502	406	1500	502	406	1500		
10	250	533	477	500	533	448	500	533	448	500	-	-	-	-	-	-		
BODY	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
BONNET / CAP	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
STEM	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
BALL	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel					
SEAT	HYPATITE® PTFE			HYPATITE® PTFE			HYPATITE® PTFE			HYPATITE® PTFE			HYPATITE® PTFE					
	Full Port SIZE:10 Gear operation type			Full Port SIZE:10 Gear operation type			Full Port SIZE:10 Gear operation type			Full Port			Full Port					

Brass & Bronze
Cast Iron
Ductile Iron
Stainless Steel
Carbon Steel
Buttery Valve
Ball Valve
Ball Valve Seat
Actuated Valve