



TYPE	3WAY FLOATING BALL				3WAY FLOATING BALL				3WAY FLOATING BALL				3WAY FLOATING BALL				3WAY FLOATING BALL			
Ball Valve																				
FIG	10UTB2T				10UTB2TM				10UTB2L				10UTB2L				10UTB2LM			
PRESSURE	10K				10K				10K				10K				10K			
END CONNECTION	JIS B2220				JIS B2220				JIS B2220				JIS B2220				JIS B2220			
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1	25	165	124	160	165	124	160	165	124	160	—	—	—	165	124	160	—	—	—
	1½	40	210	115	230	210	115	230	210	115	230	—	—	—	210	115	230	—	—	—
	2	50	220	123	230	220	123	230	220	123	230	—	—	—	220	123	230	—	—	—
	2½	65	250	155	400	250	155	400	250	155	400	—	—	—	250	155	400	—	—	—
	3	80	260	165	400	260	165	400	260	165	400	—	—	—	260	165	400	—	—	—
	4	100	330	200	460	330	200	460	330	200	460	—	—	—	330	200	460	—	—	—
	6	150	—	—	—	—	—	—	—	—	—	430	220	460	—	—	—	—	—	—
BODY	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
CAP	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
STEM	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
BALL	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
SEAT	HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE			
	Full Port				Full Port				Full Port				Reduced Port				Full Port			

TYPE	3WAY FLOATING BALL				3WAY FLOATING BALL				3WAY FLOATING BALL				3WAY FLOATING BALL				FLOATING BALL			
Ball Valve																				
FIG	10UTB4LA				10UTB4LAM				10UTB4TA				10UTB4TAM				10UTBLN			
PRESSURE	10K				10K				10K				10K				10K			
END CONNECTION	JIS B2220				JIS B2220				JIS B2220				JIS B2220				JIS B2220			
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1½	15	120	128	160	120	128	160	120	128	160	120	128	160	140	104	130	—	—	—
	¾	20	140	132	160	140	132	160	140	132	160	140	132	160	152	106	130	—	—	—
	1	25	160	135	160	160	135	160	160	135	160	160	135	160	165	129	160	—	—	—
	1½	40	180	146	400	180	146	400	180	146	400	180	146	400	191	118	230	—	—	—
	2	50	200	155	400	200	155	400	200	155	400	200	155	400	216	124	230	—	—	—
	2½	65	240	185	460	240	185	460	240	185	460	240	185	460	240	157	400	—	—	—
	3	80	260	198	460	260	198	460	260	198	460	260	198	460	250	166	400	—	—	—
	4	100	330	267	1000	330	267	1000	330	267	1000	330	267	1000	280	204	460	—	—	—
	6	150	450	335	1500	450	335	1500	450	335	1500	450	335	1500	—	—	—	—	—	—
BODY	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
CAP	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
STEM	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
BALL	Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
SEAT	HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE				HYPATITE® PTFE			
	Full Port				Full Port				Full Port				Full Port				Full Port PFA Lining			