



TYPE	FLOATING BALL					FLOATING BALL					FLOATING BALL					FLOATING BALL					FLOATING BALL				
Ball Valve																									
FIG	150UTDZ6H / G-150UTDZ6H					150UTDZ6HM / G-150UTDZ6HM					300UTDZ6H / G-300UTDZ6H					300UTDZ6HM / G-300UTDZ6HM					150UTDZXL / G-150UTDZXL				
PRESSURE	Class 150					Class 150					Class 300					Class 300					Class 150				
END CONNECTION	ASME B16.5					ASME B16.5					ASME B16.5					ASME B16.5					ASME B16.5				
DIMENSIONS	inch																								
	mm																								
	1/2	15	108	108	130	108	108	130	140	108	130	140	108	130	108	228	130								
	3/4	20	117	111	130	117	111	130	152	111	130	152	111	130	117	231	130								
	1	25	127	124	160	127	124	160	165	124	160	165	124	160	127	268	160								
	1 1/4	32	140	128	160	140	128	160	-	-	-	-	-	-	140	272	160								
	1 1/2	40	165	134	230	165	134	230	190	139	600	190	139	600	165	300	230								
	2	50	178	148	300	178	148	300	216	148	600	216	148	600	178	309	230								
	2 1/2	65	190	209	600	190	209	600	241	209	1000	241	209	1000	190	373	400								
	3	80	203	219	600	203	219	600	283	219	1000	283	219	1000	203	383	400								
	4	100	229	251	1000	229	251	1000	305	286	360	305	286	360	229	458	750								
5	125	356	302	360	356	302	360	-	-	-	-	-	-	356	482	310									
6	150	394	335	360	394	335	360	403	360	500	403	360	500	394	572	360									
8	200	457	417	500	457	417	500	502	489	500	502	489	500	457	685	500									
10	250	-	-	-	-	-	-	-	-	-	-	-	-	533	724	500									
BODY	Stainless Steel					Stainless Steel					Stainless Steel					Stainless Steel									
CAP	Stainless Steel					Stainless Steel					Stainless Steel					Stainless Steel									
STEM	Stainless Steel					Stainless Steel					Stainless Steel					Stainless Steel									
BALL	Stainless Steel+SFNi					Stainless Steel+SFNi					Stainless Steel+SFNi					Stainless Steel+SFNi									
SEAT	Stainless Steel+SFNi					Stainless Steel+SFNi					Stainless Steel+SFNi					Stainless Steel+SFNi									
	Full Port SIZE.5 to 8 Gear operation type					Full Port SIZE.5 to 8 Gear operation type					Full Port SIZE.4 to 8 Gear operation type					Full Port SIZE.4 to 8 Gear operation type									

TYPE	FLOATING BALL					FLOATING BALL					FLOATING BALL					FLOATING BALL					FLOATING BALL				
Ball Valve																									
FIG	300UTDZXL / G-300UTDZXL					SCKT					10SCTDZ / G-10SCTDZ					20SCTDZ					150SCTDZ / G-150SCTDZ				
PRESSURE	Class 300					TYPE 600					10K					20K					Class 150				
END CONNECTION	ASME B16.5					BS21 (JIS B0203)					JIS B2220					JIS B2220					ASME B16.5				
DIMENSIONS	inch																								
	mm																								
	1/4	8	-	-	-	39	31	60	-	-	-	-	-	-	-	-	-								
	3/8	10	-	-	-	44	36	70	-	-	-	-	-	-	-	-	-								
	1/2	15	140	228	130	56.5	39	85	108	108	130	140	108	130	108	108	130								
	3/4	20	152	231	130	59	43	85	117	111	130	152	111	130	117	111	130								
	1	25	165	268	160	71	48	100	127	124	160	165	124	160	127	124	160								
	1 1/4	32	-	-	-	78	53	100	-	-	-	-	-	-	-	-	-								
	1 1/2	40	190	300	230	83	62	125	165	134	230	190	134	230	165	134	230								
	2	50	216	309	230	100	70	125	178	143	230	216	143	230	178	143	230								
	2 1/2	65	241	373	400	-	-	-	190	179	400	241	179	400	190	179	400								
3	80	283	383	400	-	-	-	203	189	400	283	189	400	203	189	400									
4	100	305	466	310	-	-	-	229	224	460	305	251	750	229	224	460									
5	125	-	-	-	-	-	-	356	240	460	381	267	750	356	240	460									
6	150	403	569	500	-	-	-	394	315	1000	403	315	1000	394	315	1000									
8	200	502	685	500	-	-	-	457	406	1500	502	406	1500	457	406	1500									
10	250	-	-	-	-	-	-	533	448	500	-	-	-	533	448	500									
BODY	Stainless Steel					Cast Steel					Cast Steel					Cast Steel									
CAP	Stainless Steel					-					Cast Steel					Cast Steel									
STEM	Stainless Steel					Stainless Steel					Stainless Steel					Stainless Steel									
BALL	Stainless Steel					Stainless Steel					Stainless Steel					Stainless Steel									
SEAT	HYPATITE® PTFE					G/F PTFE					HYPATITE® PTFE					HYPATITE® PTFE									
	Full Port SIZE.4 to 8 Gear operation type					Reduced Port					Full Port SIZE.10 Gear operation type					Full Port									

Bronze & Brass
Cast Iron
Ductile Iron
Stainless Steel
Carbon Steel
Buttery Valve
Ball Valve
Ball Valve Seat
Actuated Valve