

# NANSIN WHEELS



**NMC100/NH**  
(For STC/SU-STC SERIES CASTERS)  
Nylon

(mm)	(mm)	(mm)	(mm)	(kgs)
100	32	12	42	120
200	45	20	55	250



**MHC**  
(For STH SERIES CASTERS)  
MC Nylon  
Radial bearing

(mm)	(mm)	(mm)	(mm)	(kgs)
100	50	12	53.5	520
130	50	20	58.5	840
150	50	20	58.5	1000



**NB**  
(For STC/SU-STC/SSC SERIES CASTERS)  
Nylon  
Needle bearing

(mm)	(mm)	(mm)	(mm)	(kgs)
100	29	12	45	100
125	35	12	56	140
150	35	12	56	160



**PH**  
(For THN SERIES CASTERS)  
Phenolic  
Needle bearing(65,75mm only)

(mm)	(mm)	(mm)	(mm)	(kgs)
50	28	8	32.0	150
65	38	12	41.5	210
75	38	12	41.5	220



**NL**  
(For SU-SELL SERIES CASTERS)  
Nylon

(mm)	(mm)	(mm)	(mm)	(kgs)
65	20	6	23	30
75	20	6	23	40



**PH100**  
(For THN SERIES CASTERS)  
Phenolic

(mm)	(mm)	(mm)	(mm)	(kgs)
100	32	12	42	180



**MBC**  
(For STM SERIES CASTERS)  
MC Nylon  
Radial bearing

(mm)	(mm)	(mm)	(mm)	(kgs)
75	32	10	35.6	360
100	34	12	41.0	520
130	42	20	52.0	840
150	44	20	55.0	1000
200	45	20	55.0	1330