

# Double Edge Cutting

## NOGA KEYWAY-BURR NG3300

Efficiently removes burrs from internal and external keyways. Range: 2.4-11 mm.  
INCLUDES: NG-3 handle, K holder and N80K blade.



## NOGA V CUT NG3200

For deburring sheet metal. Range: 1-8 mm.  
INCLUDES: NG-3 handle, L holder and L3 blade.



## NOGA MINI CUT NG3220

Used for deburring small ridges in difficult to reach places. Range: 0-2.5 mm.  
INCLUDES: NG-3 handle, L holder and L4 blade.



## NOGA O-RING BURR NG1100

Removes burrs from internal O-ring grooves. Range 0-3 mm (groove width).  
INCLUDES: NG-1 handle and O-ring blade.



## NOGA DOUBLE-BURR DB1000

Simultaneously removes burrs from both sides of sheet metal. DB handle with safety guard to protect your hand. Unique round cutting blades can be rotated and reversed for long life. For corners, use one blade only. Range: 0-12mm.  
INCLUDES: DB handle, handguard and two N80 blades.

