

PushOne® E Series

Shape list

Connector
EC



P.52

Hexagon socket connector
EC*-A



P.52

Internal connector
EFC



P.53

90 degree elbow
EL



P.53

90 degree internal elbow
EFL



P.54

90 degree long elbow
ELL



P.54

45 degree elbow
E45L



P.55

Universal elbow
ELB



P.55

90 degree branch elbow
ELY



P.56

Universal branch elbow
ELYB



P.56

Double universal elbow
ELWB



P.56

Triple universal elbow
ELTB



P.57

Tee
ET



P.57

Service tee
EST



P.58

Y joint
EY



P.59

Union connector
EUC



P.59

90 degree union elbow
EUL



P.60

90 degree branch elbow
EULY



P.60

Union tee
EUT



P.61

Y union
EYB



P.61

Double Y union
EUWY



P.62

Panel touch connector
EPC



P.62

Internal panel touch connector
EPFC



P.62

90 degree panel touch elbow
EPL



P.63

Reducer
ER



P.63

Adopter elbow
EAL



P.63

Y plug
EYA



P.64

Manifold A type
EMA



P.64

Manifold B type
EMB



P.64

Tube cap
ECC



P.65

Blank plug
BC



P.65

Nipple
EN



P.65

Tube

Clean tube

Processed tube

PushOne fitting

QuickSeal fitting

Clean fitting/ Chemifit

Bamboo-shoot fitting

Control switch/ Detachable series

Jig/Tool/ Accessory

Technical information

Reference