

**PB 400**

**Classic screwdrivers**

- for Torx®-screws
- precise, true-to-size tips, optimal fit in the screw heads
- slim handle, compact and for universal applications
- high-quality materials used, impact-resistant and oil/gasoline resistant
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

**Destornillador Classic**

- para tornillos Torx®
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- mango delgado, compacto y de uso universal
- acabado de alta calidad, resistente a los golpes, al aceite y a la gasolina
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 400.3-40	3	1	2.5	40	113	-	13	10	7 610733 030774	
PB 400.4-40	4	1	2.5	40	113	-	14	10	7 610733 030781	
PB 400.5-50	5	1.6	3	50	123	-	14	10	7 610733 030798	
PB 400.6-50	6	2	3	50	125	-	13	10	7 610733 007707	
PB 400.7-50	7	2	3	50	130	-	19	10	7 610733 007714	
PB 400.8-60	8	2.5	3	60	150	-	26	10	7 610733 007721	
PB 400.9-60	9	2.5	3.5	60	155	-	33	10	7 610733 007738	
PB 400.10-70	10	3	3.5	70	165	-	34	10	7 610733 007745	
PB 400.15-80	15	3.5	4	80	180	-	46	10	7 610733 007752	
PB 400.20-100	20	4	5	100	205	-	62	10	7 610733 007769	
PB 400.25-120	25	5	6	120	225	-	76	10	7 610733 007776	
PB 400.27-125	27	5-6	6	125	230	10	82	10	7 610733 015191	
PB 400.30-130	30	6	7	130	240	10	110	10	7 610733 007783	
PB 400.40-140	40	8	8	140	260	13	158	10	7 610733 007790	