

PB 8200 S

SwissGrip socket screwdrivers, with hexagonal wrench section

- for hex screws
- with hexagonal wrench section for applying higher torques and loosening tight screws
- convex handle with soft surface, pleasant grip and high torque transmission
- color coded by screw type, quick identification
- high-quality materials used, resistant to solvents, oils, acids and salts
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave de vaso con mango SwissGrip, con extremo hexagonal

- para tornillos hexagonales
- con extremo hexagonal para aplicar pares de torsión elevados y aflojar tornillos apretados
- mango arqueado con superficie suave, sensación de agarre agradable y transmisión de par de torsión elevada
- codificación por colores según el tipo de tornillo, identificación rápida
- acabado de alta calidad, resistente a los disolventes, aceites, ácidos y sales
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 8200.S 8-120	5	120	230	10	101		10	7 610733 068616
PB 8200.S 9-140	-	140	250	10	120		10	7 610733 068623
PB 8200.S 10-160	6	160	270	10	133		10	7 610733 068630
PB 8200.S 11-180	7	180	300	13	183		10	7 610733 068647
PB 8200.S 12-190	-	190	310	13	210		10	7 610733 068654
PB 8200.S 13-200	8	200	320	17	262		10	7 610733 068661

PB 8205

SwissGrip screwdrivers

- for hexagon socket screws
- precise, true-to-size tips, optimal fit in the screw heads
- convex handle with soft surface, pleasant grip and high torque transmission
- color coded by screw type, quick identification
- high-quality materials used, resistant to solvents, oils, acids and salts
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Destornillador SwissGrip

- para tornillos con hexágono interior
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- mango arqueado con superficie suave, sensación de agarre agradable y transmisión de par de torsión elevada
- codificación por colores según el tipo de tornillo, identificación rápida
- acabado de alta calidad, resistente a los disolventes, aceites, ácidos y sales
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 8205.0,71-40	0.71	1.4	-	40	117	13	10	7 610733 089253
PB 8205.0,89-40	0.89	2	-	40	117	13	10	7 610733 089260
PB 8205.1,27-50	1.27	2.5	1.4	50	127	11	10	7 610733 089277
PB 8205.1,5-70	1.5	3	1.6-2	70	147	13	10	7 610733 089284
PB 8205.2-80	2	4	2.5	80	157	14	10	7 610733 089291
PB 8205.2,5-90	2.5	5	3	90	170	20	10	7 610733 079100
PB 8205.3-100	3	6	4	100	190	29	10	7 610733 079117
PB 8205.4-120	4	8	5	120	220	50	10	7 610733 079124
PB 8205.5-140	5	10	6	140	245	73	10	7 610733 079131
PB 8205.6-160	6	12-14	8	160	270	103	10	7 610733 079148
PB 8205.8-180	8	16	10	180	300	167	10	7 610733 079155