

PB 1207

Cross-handle screwdriver, with side drive

- for hexagon socket screws
- precise, true-to-size tips, optimal fit in the screw heads
- cross-handle with side drive, for applying high torques
- high-quality materials used, resistant to solvents, oils, acids and salts
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Destornillador con mango transversal y terminación lateral

- para tornillos con hexágono interior
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- mango transversal con terminación lateral, para aplicar pares de apriete elevados
- acabado de alta calidad, resistente a los disolventes, aceites, ácidos y sales
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 1207.4-150	4	8	5	125	150	187	18	92	53	10	7 610733 256525	
PB 1207.5-150	5	10	6	125	150	187	18	92	66	10	7 610733 256532	
PB 1207.6-150	6	12-14	8	125	155	200	20	117	117	10	7 610733 256549	
PB 1207.8-150	8	16	10	125	155	200	20	117	164	10	7 610733 256556	
PB 1207.10-200	10	18-20	12	167	198	245	22	119	213	10	7 610733 256563	