

PB 1406

Cross-handle screwdrivers

- for Torx®-screws
- precise, true-to-size tips, optimal fit in the screw heads
- ergonomically-designed cross-handle, keeps the wrist properly aligned and reduces strain
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Destornillador con mango transversal

- para tornillos Torx®
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- mango transversal ergonómico; mantiene la muñeca recta y la protege
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



6-15

NEW

NEW											
PB 1406.6-60	6	2	3	60	-	105	48	14		10	7 610733 287482
PB 1406.7-60	7	2	3	60	-	105	48	14		10	7 610733 287499
PB 1406.8-60	8	2.5	3	60	-	105	48	14		10	7 610733 287505
PB 1406.9-60	9	2.5	3.5	60	-	105	48	16		10	7 610733 287512
PB 1406.10-60	10	3	3.5	60	-	105	48	16		10	7 610733 287529
PB 1406.15-60	15	3.5	4	60	-	105	48	18		10	7 610733 287536
PB 1406.20-80	20	4	5	55	80	117	73	45		10	7 610733 287543
PB 1406.25-80	25	5	6	55	80	117	73	54		10	7 610733 287550

PB 1407

Cross-handle screwdriver, with side drive

- for Torx®-screws
- precise, true-to-size tips, optimal fit in the screw heads
- cross-handle with side drive, for applying high torques
- high-quality materials used, resistant to solvents, oils, acids and salts
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Destornillador con mango transversal y terminación lateral

- para tornillos Torx®
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- mango transversal con terminación lateral, para aplicar pares de apriete elevados
- acabado de alta calidad, resistente a los disolventes, aceites, ácidos y sales
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



20-30

PB 1407.20-150	20	4	4	125	150	187	18	92	66	10	7 610733 256693
PB 1407.25-150	25	5	5	125	150	187	20	92	81	10	7 610733 256709
PB 1407.30-150	30	6	6	125	150	187	20	94	102	10	7 610733 256716
PB 1407.40-200	40	8	7	170	200	245	22	119	182	10	7 610733 256723