

PB 215 D

Interchangeable blade for PB 215 A, 8215 A, DigiTorque and MecaTorque handles

- for hexagon socket screws
- precise, true-to-size tips, optimal fit in the screw heads
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Hoja intercambiable para mangos PB 215 A, 8215 A, DigiTorque y MecaTorque

- para tornillos con hexágono interior
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 215.D 1,5	1.5	1.6-2	70	150	28	10	7 610733 205288
PB 215.D 2	2	2.5	80	160	28	10	7 610733 205295
PB 215.D 2,5	2.5	3	90	170	28	10	7 610733 038756
PB 215.D 3	3	4	100	180	28	10	7 610733 038763
PB 215.D 4	4	5	110	190	35	10	7 610733 038770
PB 215.D 5	5	6	125	205	43	10	7 610733 038787
PB 215.D 6	6	8	140	220	56	10	7 610733 038794

PB 215 T

Interchangeable blade for PB 215 A, 8215 A, DigiTorque and MecaTorque handles

- for Torx®-screws
- precise, true-to-size tips, optimal fit in the screw heads
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Hoja intercambiable para mangos PB 215 A, 8215 A, DigiTorque y MecaTorque

- para tornillos Torx®
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 215.T 6	6	2	3	70	150	27	7 610733 069323
PB 215.T 7	7	2	3	70	150	27	7 610733 069330
PB 215.T 8	8	2.5	3.5	80	160	28	7 610733 044603
PB 215.T 9	9	2.5	3.5	80	160	28	7 610733 044658
PB 215.T 10	10	3	4	90	170	29	7 610733 044610
PB 215.T 15	15	3.5	4	100	180	34	7 610733 044627
PB 215.T 20	20	4	5	110	190	39	7 610733 044634
PB 215.T 25	25	5	6	120	200	42	7 610733 044641
PB 215.T 30	30	5	6	120	200	43	7 610733 071531