

PB 225 T
Interchangeable blade for articulated handle PB 225 A, DigiTorque and MecaTorque lever handles

- for Torx®-screws
- precise, true-to-size tips, optimal fit in the screw heads
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Hoja intercambiable para mango abatible PB 225 A, mangos de palanca DigiTorque y MecaTorque

- para tornillos Torx®
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 225.T 15	15	3.5	120	19	10	7 610733 216611
PB 225.T 20	20	4	140	27	10	7 610733 216628
PB 225.T 25	25	5	160	38	10	7 610733 069552
PB 225.T 30	30	6	160	49	10	7 610733 069569
PB 225.T 40	40	8	160	58	10	7 610733 069576
PB 225.T 45	45	10	160	59	10	7 610733 069583

PB 225 F
Interchangeable blade for articulated handle PB 225 A, DigiTorque and MecaTorque lever handles

- for hex screws
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Hoja intercambiable para mango abatible PB 225 A, mangos de palanca DigiTorque y MecaTorque

- para tornillos hexagonales
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación láser con n.º de serie, garantía de por vida



PB 225.F 5,5	3	90	22		10	7 610733 044337
PB 225.F 6	3.5	90	26		10	7 610733 044344
PB 225.F 7	4	100	35		10	7 610733 044351
PB 225.F 8	5	110	39		10	7 610733 044368
PB 225.F 9	-	120	42		10	7 610733 044375
PB 225.F 10	6	140	63		10	7 610733 044382
PB 225.F 11	7	160	70		10	7 610733 044399
PB 225.F 12	-	170	87		10	7 610733 044405
PB 225.F 13	8	180	112		10	7 610733 044412