

PB 210 RB

RainBow key L-wrenches

- for hexagon socket screws
- chrome-plated and powder-coated, color coded by size, quick access to the right tool
- precisely chamfered edges, ensures easy insertion into screws
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada RainBow

- para tornillos con hexágono interior
- cromado y con recub. electrostático, cod. de color según tamaño; la herramienta adecuada siempre a mano
- bordes quebrados precisos, inserción segura en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación con n.º de serie; garantía de por vida



									
PB 210.1,5 LG		1.5	3	1.6-2	14	50	1	10	7 610733 077069
PB 210.2 GR		2	4	2.5	16	56	2	10	7 610733 077076
PB 210.2,5 YG		2.5	5	3	18	63	3	10	7 610733 077083
PB 210.3 SY		3	6	4	20	71	5	10	7 610733 077090
PB 210.4 YE		4	8	5	22	80	11	10	7 610733 077106
PB 210.5 OR		5	10	6	25	90	19	10	7 610733 077113
PB 210.6 RE		6	12-14	8	28	100	31	10	7 610733 077120
PB 210.8 PU		8	16	10	32	112	62	10	7 610733 077137
PB 210.10 BL		10	18-20	12	36	125	109	10	7 610733 077144

PB 212 RB

RainBow key L-wrenches with ball point

- for hexagon socket screws
- chrome-plated and powder-coated, color coded by size, quick access to the right tool
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada RainBow con cabeza esférica

- para tornillos con hexágono interior
- cromado y con recub. electrostático, cod. de color según tamaño; la herramienta adecuada siempre a mano
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación con n.º de serie; garantía de por vida



									
PB 212.1,5 LG		1.5	3	1.6-2	14	50	1	10	7 610733 063758
PB 212.2 GR		2	4	2.5	16	56	2	10	7 610733 063765
PB 212.2,5 YG		2.5	5	3	18	63	3.5	10	7 610733 063772
PB 212.3 SY		3	6	4	20	71	5.5	10	7 610733 063789
PB 212.4 YE		4	8	5	22	80	12	10	7 610733 063796
PB 212.5 OR		5	10	6	25	90	20	10	7 610733 063802
PB 212.6 RE		6	12-14	8	28	100	31	10	7 610733 063819
PB 212.8 PU		8	16	10	32	112	60	10	7 610733 063826
PB 212.10 BL		10	18-20	12	36	125	105	10	7 610733 063833