

**PB 212 H RB**

**RainBow key L-wrenches with ball point, set in a practical plastic holder**

- for hexagon socket screws
- chrome-plated and powder-coated, color coded by size, quick access to the right tool
- perfectly shaped ball point, allows screws to be turned at an angle of up to 30°
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

**Llaves acodadas RainBow con cabeza esférica; juego en práctico soporte de plástico**

- para tornillos con hexágono interior
- cromado y con recub. electrostático, cod. de color según tamaño; la herramienta adecuada siempre a mano
- cabeza esférica de forma perfecta, que permite girar tornillos con un ángulo de hasta 30°
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación con n.º de serie; garantía de por vida



				
PB 212.H-5 RB	1.5, 2, 2.5, 3, 4, 5	51	10	7 610733 254262
PB 212.H-6 RB	1.5, 2, 2.5, 3, 4, 5, 6	84	10	7 610733 254279
PB 212.H-10 RB	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	254	10	7 610733 063741

**In blister packs**

**En embalaje blíster**

				
PB 212.H-10 RB CN	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	278	10	7 610733 236299