

PB 410 RB

RainBow key L-wrenches

- for Torx®-screws
- chrome-plated and powder-coated, color coded by size, quick access to the right tool
- precise, true-to-size tips, optimal fit in the screw heads
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llave acodada RainBow

- para tornillos Torx®
- cromado y con recub. electrostático, cod. de color según tamaño; la herramienta adecuada siempre a mano
- puntas precisas de dimensiones exactas; ajuste óptimo en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación con n.º de serie; garantía de por vida



PB 410.6 GR		6	2	2.5	15	52	2	10	7 610733 243860
PB 410.7 YG		7	2	2.5	16	56	2	10	7 610733 243877
PB 410.8 SY		8	2.5	2.5	17	60	3	10	7 610733 243884
PB 410.9 YE		9	2.5	3	17	63	4	10	7 610733 243891
PB 410.10 OR		10	3	3.5	18	67	6	10	7 610733 243907
PB 410.15 RE		15	3.5	3.5	20	72	7	10	7 610733 243914
PB 410.20 PU		20	4	4	21	77	9	10	7 610733 243921
PB 410.25 BL		25	5	5	22	83	15	10	7 610733 243938

PB 410 H RB

RainBow key L-wrenches, set in a practical plastic holder

- for Torx®-screws
- chrome-plated and powder-coated, color coded by size, quick access to the right tool
- precise, true-to-size tips, optimal fit in the screw heads
- special alloy based on spring steel, exceptional elasticity coupled with high grade hardening
- laser-marked serial number, lifetime guarantee

Llaves acodadas RainBow; juego en práctico soporte de plástico

- para tornillos Torx®
- cromado y con recub. electrostático, cod. de color según tamaño; la herramienta adecuada siempre a mano
- puntas precisas de dimensiones exactas; ajuste óptimo en los tornillos
- aleación especial de acero para resortes, elasticidad extraordinaria y gran dureza
- rotulación con n.º de serie; garantía de por vida



PB 410.H 6-25 RB	6, 7, 8, 9, 10, 15, 20, 25	63	10	7 610733 244027

**In blister packs
En embalaje blister**

PB 410.H 6-25 RB CN	6, 7, 8, 9, 10, 15, 20, 25	78	10	7 610733 244089