









The products listed in this page are ECO-friendly products.

* Please refer to page 4 for the details of ECO-friendly products.

PAX Branch Elbow 	Model type		Model type	PHW Double Banjo 	Model type		Model type	PHT Triple Banjo 	Model type		Model type
	Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg
PVX Tripod Elbow 	Model type		Model type	PAW Double Twin Banjo 	Model type		Model type	PAT Triple Twin Banjo 	Model type		Model type
	Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg
	PAXoD-T ④	PAXoD-TU	PAXoD-T ④ C		PHWoD-T ④	PHWoD-TU	PHWoD-T ④ C		PHToD-T ④	PHToD-TU	PHToD-T ④ C
	PAX4-M5 ④	PAX ^{5/32} -U10U	PAX4-M5 ④ C		PHW4-01 ④	PHW ^{5/32} -N1U	PHW4-01 ④ C		PHT4-01 ④	PHT ^{5/32} -N1U	PHT4-01 ④ C
	PAX4-M6 ④	PAX ^{5/32} -N1U	PAX4-M6 ④ C		PHW4-02 ④	PHW ^{5/32} -N2U	PHW4-02 ④ C		PHT4-02 ④	PHT ^{5/32} -N2U	PHT4-02 ④ C
	PAX4-01 ④	PAX ^{5/32} -N2U	PAX4-01 ④ C		PHW4-03 ④	PHW ^{1/4} -N1U	PHW4-03 ④ C		PHT4-03 ④	PHT ^{1/4} -N1U	PHT4-03 ④ C
	PAX4-02 ④	PAX ^{3/16} -U10U	PAX4-02 ④ C		PHW6-01 ④	PHW ^{1/4} -N2U	PHW6-01 ④ C		PHT6-01 ④	PHT ^{1/4} -N2U	PHT6-01 ④ C
	PAX6-M5 ④	PAX ^{3/16} -N1U	PAX6-M5 ④ C		PHW6-02 ④	PHW ^{1/4} -N3U	PHW6-02 ④ C		PHT6-02 ④	PHT ^{1/4} -N3U	PHT6-02 ④ C
	PAX6-M6 ④	PAX ^{3/16} -N2U	PAX6-M6 ④ C		PHW6-03 ④	PHW ^{5/16} -N2U	PHW6-03 ④ C		PHT6-03 ④	PHT ^{5/16} -N2U	PHT6-03 ④ C
	PAX6-01 ④	PAX ^{3/16} -N3U	PAX6-01 ④ C		PHW8-01 ④	PHW ^{5/16} -N3U	PHW8-01 ④ C		PHT8-01 ④	PHT ^{5/16} -N3U	PHT8-01 ④ C
	PAX6-02 ④	PAX ^{1/4} -U10U	PAX6-02 ④ C		PHW8-02 ④	PHW ^{5/16} -N4U	PHW8-02 ④ C		PHT8-02 ④	PHT ^{5/16} -N4U	PHT8-02 ④ C
	PAX6-03 ④	PAX ^{1/4} -N1U	PAX6-03 ④ C		PHW8-03 ④	PHW ^{3/8} -N2U	PHW8-03 ④ C		PHT8-03 ④	PHT ^{3/8} -N2U	PHT8-03 ④ C
	PAX8-01 ④	PAX ^{1/4} -N2U	PAX8-01 ④ C		PHW8-04 ④	PHW ^{3/8} -N3U	PHW8-04 ④ C		PHT8-04 ④	PHT ^{3/8} -N3U	PHT8-04 ④ C
	PAX8-02 ④	PAX ^{1/4} -N3U	PAX8-02 ④ C		PHW10-02 ④	PHW ^{3/8} -N4U	PHW10-02 ④ C		PHT10-02 ④	PHT ^{3/8} -N4U	PHT10-02 ④ C
	PAX8-03 ④	PAX ^{5/16} -N1U	PAX8-03 ④ C		PHW10-03 ④	PHW ^{1/2} -N3U	PHW10-03 ④ C		PHT10-03 ④	PHT ^{1/2} -N3U	PHT10-03 ④ C
	PAX10-01 ④	PAX ^{5/16} -N2U	PAX10-01 ④ C		PHW10-04 ④	PHW ^{1/2} -N4U	PHW10-04 ④ C		PHT10-04 ④	PHT ^{1/2} -N4U	PHT10-04 ④ C
	PAX10-02 ④	PAX ^{3/8} -N3U	PAX10-02 ④ C		PHW12-02 ④	PHW8-N3U **	PHW12-02 ④ C		PHT12-02 ④		PHT12-02 ④ C
	PAX10-03 ④	PAX ^{3/8} -N1U	PAX10-03 ④ C		PHW12-03 ④	PHW10-N4U **	PHW12-03 ④ C		PHT12-03 ④		PHT12-03 ④ C
	PAX10-04 ④	PAX ^{3/8} -N2U	PAX10-04 ④ C		PHW12-04 ④	PHW12-N4U **	PHW12-04 ④ C		PHT12-04 ④		PHT12-04 ④ C
	PAX12-02 ④	PAX ^{3/8} -N3U	PAX12-02 ④ C		PHW ^{1/4} -01 ④		PHW ^{1/4} -01 ④ C		PHT ^{1/4} -01 ④		PHT ^{1/4} -01 ④ C
	PAX12-03 ④	PAX ^{3/8} -N4U	PAX12-03 ④ C		PHW ^{1/4} -02 ④		PHW ^{1/4} -02 ④ C		PHT ^{1/4} -02 ④		PHT ^{1/4} -02 ④ C
	PAX12-04 ④	PAX ^{1/2} -N2U	PAX12-04 ④ C		PHW ^{1/4} -03 ④		PHW ^{1/4} -03 ④ C		PHT ^{1/4} -03 ④		PHT ^{1/4} -03 ④ C
PKD Triple Run Tee 	Model type		Model type	PRJ Plug-in Double Y 	Model type		Model type	PKJ Plug-in Triple Tee 	Model type		Model type
	Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg
	PVXoD-T ④	PVXoD-TU	PVXoD-T ④ C		PAWoD-T ④	PAWoD-TU	PAWoD-T ④ C		PAToD-T ④	PAToD-TU	PAToD-T ④ C
	PVX4-M5 ④	PVX ^{5/32} -U10U	PVX4-M5 ④ C		PAW4-01 ④	PAW ^{5/32} -N1U	PAW4-01 ④ C		PAT4-01 ④	PAT ^{5/32} -N1U	PAT4-01 ④ C
	PVX4-M6 ④	PVX ^{5/32} -N1U	PVX4-M6 ④ C		PAW4-02 ④	PAW ^{5/32} -N2U	PAW4-02 ④ C		PAT4-02 ④	PAT ^{5/32} -N2U	PAT4-02 ④ C
	PVX4-01 ④	PVX ^{5/32} -N2U	PVX4-01 ④ C		PAW4-03 ④	PAW ^{1/4} -N1U	PAW4-03 ④ C		PAT4-03 ④	PAT ^{1/4} -N1U	PAT4-03 ④ C
	PVX4-02 ④	PVX ^{3/16} -U10U	PVX4-02 ④ C		PAW6-01 ④	PAW ^{1/4} -N2U	PAW6-01 ④ C		PAT6-01 ④	PAT ^{1/4} -N2U	PAT6-01 ④ C
	PVX6-M5 ④	PVX ^{3/16} -N1U	PVX6-M5 ④ C		PAW6-02 ④	PAW ^{1/4} -N3U	PAW6-02 ④ C		PAT6-02 ④	PAT ^{1/4} -N3U	PAT6-02 ④ C
	PVX6-M6 ④	PVX ^{3/16} -N2U	PVX6-M6 ④ C		PAW6-03 ④	PAW ^{5/16} -N2U	PAW6-03 ④ C		PAT6-03 ④	PAT ^{5/16} -N1U **	PAT6-03 ④ C
	PVX6-01 ④	PVX ^{3/16} -N3U	PVX6-01 ④ C		PAW8-01 ④	PAW ^{5/16} -N3U	PAW8-01 ④ C		PAT8-01 ④	PAT ^{5/16} -N2U	PAT8-01 ④ C
	PVX6-02 ④	PVX ^{1/4} -U10U	PVX6-02 ④ C		PAW8-02 ④	PAW ^{5/16} -N4U	PAW8-02 ④ C		PAT8-02 ④	PAT ^{5/16} -N3U	PAT8-02 ④ C
	PVX6-03 ④	PVX ^{1/4} -N1U	PVX6-03 ④ C		PAW8-03 ④	PAW ^{3/8} -N2U	PAW8-03 ④ C		PAT8-03 ④	PAT ^{5/16} -N4U	PAT8-03 ④ C
	PVX8-01 ④	PVX ^{1/4} -N2U	PVX8-01 ④ C		PAW8-04 ④	PAW ^{3/8} -N3U	PAW8-04 ④ C		PAT8-04 ④	PAT ^{3/8} -N2U	PAT8-04 ④ C
	PVX8-02 ④	PVX ^{1/4} -N3U	PVX8-02 ④ C		PAW10-02 ④	PAW ^{3/8} -N4U	PAW10-02 ④ C		PAT10-02 ④	PAT ^{3/8} -N3U	PAT10-02 ④ C
	PVX8-03 ④	PVX ^{5/16} -N1U	PVX8-03 ④ C		PAW10-03 ④	PAW ^{1/2} -N3U	PAW10-03 ④ C		PAT10-03 ④	PAT ^{3/8} -N4U	PAT10-03 ④ C
	PVX10-01 ④	PVX ^{5/16} -N2U	PVX10-01 ④ C		PAW10-04 ④	PAW ^{1/2} -N4U	PAW10-04 ④ C		PAT10-04 ④	PAT ^{1/2} -N3U	PAT10-04 ④ C
	PVX10-02 ④	PVX ^{3/8} -N3U	PVX10-02 ④ C		PAW12-02 ④		PAW12-02 ④ C		PAT12-02 ④	PAT ^{1/2} -N4U	PAT12-02 ④ C
	PVX10-03 ④	PVX ^{3/8} -N1U	PVX10-03 ④ C		PAW12-03 ④		PAW12-03 ④ C		PAT12-03 ④		PAT12-03 ④ C
	PVX10-04 ④	PVX ^{3/8} -N2U	PVX10-04 ④ C		PAW12-04 ④		PAW12-04 ④ C		PAT12-04 ④		PAT12-04 ④ C
	PVX12-02 ④	PVX ^{3/8} -N3U	PVX12-02 ④ C		PAW ^{1/4} -01 ④		PAW ^{1/4} -01 ④ C		PAT ^{1/4} -01 ④		PAT ^{1/4} -01 ④ C
	PVX12-03 ④	PVX ^{3/8} -N4U	PVX12-03 ④ C		PAW ^{1/4} -02 ④		PAW ^{1/4} -02 ④ C		PAT ^{1/4} -02 ④		PAT ^{1/4} -02 ④ C
	PVX12-04 ④	PVX ^{1/2} -N2U	PVX12-04 ④ C		PAW ^{1/4} -03 ④		PAW ^{1/4} -03 ④ C		PAT ^{1/4} -03 ④		PAT ^{1/4} -03 ④ C
PRX Double Branch Y 	Model type		Model type		Model type		Model type		Model type		Model type
	Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg
	PRXoD-T ④	PRXoD-TU	PRXoD-T ④ C		PRJoD-T ④	PRJoD-TU	PRJoD-T ④ C		PKJoD-T ④	PKJoD-TU	PKJoD-T ④ C
	PRX4-01 ④	PRX ^{5/32} -N1U	PRX4-01 ④ C		PRJ6-4 ④	PRJ6-4 ④ C			PKJ6-4 ④	PKJ6-4 ④ C	
	PRX4-02 ④	PRX ^{5/32} -N2U	PRX4-02 ④ C		PRJ8-6 ④	PRJ8-6 ④ C			PKJ8-6 ④	PKJ8-6 ④ C	
PRX Double Branch Y 	Model type		Model type		Model type		Model type		Model type		Model type
	Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg		Standard pkg		Clean-room pkg
	PRX6-01 ④	PRX ^{5/16} -N1U	PRX6-01 ④ C						PKJ10-8 ④	PKJ10-8 ④ C	
		PRX ^{1/4} -N1U									
		PRX ^{1/4} -N2U **									



Cautions

*1. Custom-made, build to order production

*2. The white-letter model type in is new model.

*3. ④ is replaced with "W" if Light-gray specification is required otherwise please leave it blank.

*4. The option: W, C, or WC is build to order production.

*5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.



Package specifications

10 pcs. in a bag: Standard pkg

1 pc. in a bag (10 pcs./set): Clean-room pkg