




















The products listed in this page are ECO-friendly products.
* Please refer to page 4 for the details of ECO-friendly products.


Thread material: SUS304

PPC	Model	PPL	Model	PPB	Model	PPD	Model	PPX	Model
Straight øD 	PPCøD-TSUS 6 7 8	Elbow øD 	PPLøD-TSUS 6 7 8	Branch Tee øD 	PPBøD-TSUS 6 7 8	Run Tee øD 	PPDøD-TSUS 6 7 8	Branch Y øD 	PPXøD-TSUS 6 7 8
	PPC4-M5SUS 6 7 8		PPL4-M5SUS 6 7 8		PPB4-M5SUS 6 7 8		PPD4-M5SUS 6 7 8		PPX4-M5SUS 6 7 8
	PPC4-01SUS 6 7 8		PPL4-01SUS 6 7 8		PPB4-01SUS 6 7 8		PPD4-01SUS 6 7 8		PPX4-01SUS 6 7 8
	PPC4-02SUS 6 7 8		PPL4-02SUS 6 7 8		PPB4-02SUS 6 7 8		PPD4-02SUS 6 7 8		PPX4-02SUS 6 7 8
	PPC6-M5SUS 6 7 8		PPL6-M5SUS 6 7 8		PPB6-M5SUS 6 7 8		PPD6-M5SUS 6 7 8		PPX6-M5SUS 6 7 8
	PPC6-01SUS 6 7 8		PPL6-01SUS 6 7 8		PPB6-01SUS 6 7 8		PPD6-01SUS 6 7 8		PPX6-01SUS 6 7 8
	PPC6-02SUS 6 7 8		PPL6-02SUS 6 7 8		PPB6-02SUS 6 7 8		PPD6-02SUS 6 7 8		PPX6-02SUS 6 7 8
	PPC6-03SUS 6 7 8		PPL6-03SUS 6 7 8		PPB6-03SUS 6 7 8		PPD6-03SUS 6 7 8		PPX6-03SUS 6 7 8
	PPC8-01SUS 6 7 8		PPL8-01SUS 6 7 8		PPB8-01SUS 6 7 8		PPD8-01SUS 6 7 8		PPX8-01SUS 6 7 8
	PPC8-02SUS 6 7 8		PPL8-02SUS 6 7 8		PPB8-02SUS 6 7 8		PPD8-02SUS 6 7 8		PPX8-02SUS 6 7 8
	PPC8-03SUS 6 7 8		PPL8-03SUS 6 7 8		PPB8-03SUS 6 7 8		PPD8-03SUS 6 7 8		PPX8-03SUS 6 7 8
	PPC10-02SUS 6 7 8		PPL10-02SUS 6 7 8		PPB10-02SUS 6 7 8		PPD10-02SUS 6 7 8		PPX10-02SUS 6 7 8
	PPC10-03SUS 6 7 8		PPL10-03SUS 6 7 8		PPB10-03SUS 6 7 8		PPD10-03SUS 6 7 8		PPX10-03SUS 6 7 8
	PPC12-03SUS 6 7 8		PPL12-03SUS 6 7 8		PPB12-03SUS 6 7 8		PPD12-03SUS 6 7 8		PPX12-03SUS 6 7 8
	PPC12-04SUS 6 7 8		PPL12-04SUS 6 7 8		PPB12-04SUS 6 7 8		PPD12-04SUS 6 7 8		PPX12-04SUS 6 7 8

PPU	Model	PPV	Model	PPE	Model	PPY	Model	PPMP	Model
Union Straight øD 	PPUøD 6 7	Union Elbow øD 	PPVøD 6 7	Union Tee øD 	PPEøD 6 7	Union Y øD 	PPYøD 6 7	Bulkhead Union P øD 	PPMPøD 6 7
	PPU4 6 7		PPV4 6 7		PPE4 6 7		PPY4 6 7		PPMP4 6 7
	PPU6 6 7		PPV6 6 7		PPE6 6 7		PPY6 6 7		PPMP6 6 7
	PPU8 6 7		PPV8 6 7		PPE8 6 7		PPY8 6 7		PPMP8 6 7
	PPU10 6 7		PPV10 6 7		PPE10 6 7		PPY10 6 7		PPMP10 6 7
	PPU12 6 7		PPV12 6 7		PPE12 6 7		PPY12 6 7		PPMP12 6 7
PPG	Model	PPGJ	Model	PPEG	Model	PPW	Model	PPP	Model
Unequal Union Straight øD ₁ øD ₂ 	PPGøD ₁ -øD ₂ 6 7	Plug-in Reducer øD ₁ øD ₂ 	PPGJøD ₁ -øD ₂ 6 7	Unequal Union Tee øD ₁ øD ₂ 	PPEGøD ₁ -øD ₂ 6 7	Unequal Union Y øD ₁ øD ₂ 	PPWøD ₁ -øD ₂ 6 7	Plug øD 	PPPøD 7
	PPG6-4 6 7		PPGJ6-4 6 7		PPEG6-4 6 7		PPW6-4 6 7		PPP4 7
	PPG8-6 6 7		PPGJ8-4 6 7		PPEG8-6 6 7		PPW8-6 6 7		PPP6 7
	PPG10-8 6 7		PPGJ8-6 6 7		PPEG10-8 6 7		PPW10-8 6 7		PPP8 7
	PPG12-10 6 7		PPGJ10-6 6 7		PPEG12-10 6 7		PPW12-10 6 7		PPP10 7
			PPGJ10-8 6 7						PPP12 7
			PPGJ12-8 6 7						
			PPGJ12-10 6 7						

 Caution
*5. The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.

 Package specification
1 pc. in a bag

 Options
*1. For [6](#), please select a seal rubber material.
*2. For [7](#), please select a pkg option.
*3. For [8](#), please select a thread sealing option.