




















The products listed in this page are ECO-friendly products.
* Please refer to page 4 for the details of ECO-friendly products.

Standard type (Without stop valve)

AKC Straight Tube Coms  øD T	Model		AKL Elbow Tube Coms  øD T	Model		AKC Female Screw Coms  T ₁ T	Model		AKC Straight Barb Coms  øD T	Model	
	AKC ③ -øDT	AKC ③ -øDTU		AKL ③ -øDT	AKL ③ -øDTU		AKC ③ -T ₁ FT	AKC ③ -øDBT			
	AKC08-601	AKC08-5/16N1U		AKL08-601	AKL08-5/16N1U		AKC08-01F01	AKC08-ID06B01			
	AKC08-602	AKC08-5/16N2U		AKL08-602	AKL08-5/16N2U		AKC08-01F02	AKC08-ID06B02			
	AKC08-801	AKC10-5/16N1U		AKL08-801	AKL10-5/16N1U		AKC08-02F01	AKC08-ID09B01			
	AKC08-802	AKC10-5/16N2U		AKL08-802	AKL10-5/16N2U		AKC08-02F02	AKC08-ID09B02			
	AKC10-801	AKC10-5/16N3U		AKL10-801	AKL10-5/16N3U		AKC10-01F01	AKC10-ID06B01			
	AKC10-802	AKC10-3/8N1U		AKL10-802	AKL10-3/8N1U		AKC10-01F02	AKC10-ID06B02			
	AKC10-803	AKC10-3/8N2U		AKL10-803	AKL10-3/8N2U		AKC10-01F03	AKC10-ID06B03			
	AKC10-804	AKC10-3/8N3U		AKL10-804	AKL10-3/8N3U		AKC10-01F04	AKC10-ID06B04			
	AKC10-1001			AKL10-1001			AKC10-02F01	AKC10-ID09B01			
	AKC10-1002			AKL10-1002			AKC10-02F02	AKC10-ID09B02			
	AKC10-1003			AKL10-1003			AKC10-02F03	AKC10-ID09B03			
	AKC10-1004			AKL10-1004			AKC10-02F04	AKC10-ID09B04			
AKC10-1201		AKL10-1201		AKC10-03F01							
AKC10-1202		AKL10-1202		AKC10-03F02							
AKC10-1203		AKL10-1203		AKC10-03F03							
AKC10-1204		AKL10-1204		AKC10-03F04							
AKC Straight Tube Plug  øD	Model		AKL Elbow Tube Plug  øD	Model		AKC Female Screw Plug  T ₁	Model		AKC Straight Barb Plug  øD	Model	
	AKC ③ -øDP	AKC ③ -øDP		AKL ③ -øDP	AKL ③ -øDP		AKC ③ -T ₁ FP	AKC ③ -øDBP			
	AKC08-6P	AKC08-5/16P		AKL08-6P	AKL08-5/16P		AKC08-01FP	AKC08-ID06BP			
	AKC08-8P	AKC10-5/16P		AKL08-8P	AKL10-5/16P		AKC08-02FP	AKC08-ID09BP			
	AKC10-8P	AKC10-3/8P		AKL10-8P	AKL10-3/8P		AKC10-01FP	AKC10-ID06BP			
AKC10-10P		AKL10-10P		AKC10-02FP	AKC10-ID09BP						
AKC10-12P		AKL10-12P		AKC10-03FP							
AK Screw Socket  T	Model										
	AK ③ -TS	AK ③ -TSU									
	AK08-01S	AK08-N1SU									
	AK08-02S	AK08-N2SU									
	AK10-01S	AK10-N1SU									
	AK10-02S	AK10-N2SU									
AK10-03S	AK10-N3SU										
AK10-04S											

Stop Valve Built-in type

ASC Straight Tube Coms  øD R	Model		ASL Elbow Tube Coms  øD R	Model		ASC Female Screw Coms  T ₁ T	Model		ASC Straight Barb Coms  øD T	Model	
	ASC10-øDT	ASC10-øDTU		ASL10-øDT	ASL10-øDTU		ASC10-T ₁ FT	ASC10-øDBT			
	ASC10-601	ASC10-5/16N1U		ASL10-601	ASL10-5/16N1U		ASC10-01F01	ASC10-ID06B01			
	ASC10-602	ASC10-5/16N2U		ASL10-602	ASL10-5/16N2U		ASC10-01F02	ASC10-ID06B02			
	ASC10-603	ASC10-3/8N1U		ASL10-603	ASL10-3/8N1U		ASC10-01F03	ASC10-ID06B03			
	ASC10-801	ASC10-3/8N2U		ASL10-801	ASL10-3/8N2U		ASC10-02F01	ASC10-ID09B01			
	ASC10-802	ASC10-3/8N3U		ASL10-802	ASL10-3/8N3U		ASC10-02F02	ASC10-ID09B02			
	ASC10-803			ASL10-803			ASC10-02F03	ASC10-ID09B03			
	ASC10-1001			ASL10-1001			ASC10-03F01				
	ASC10-1002			ASL10-1002			ASC10-03F02				
	ASC10-1003			ASL10-1003			ASC10-03F03				
	ASC10-1201			ASL10-1201							
	ASC10-1202			ASL10-1202							
ASC10-1203		ASL10-1203									
ASC Straight Tube Plug  øD	Model		ASL Elbow Tube Plug  øD	Model		ASC Female Screw Plug  T ₁	Model		AS Screw Socket  T	Model	
	ASC10-øDP	ASC10-øDP		ASL10-øDP	ASL10-øDP		ASC10-T ₁ FP	ASC10-øDBP			
	ASC10-6P	ASC10-5/16P		ASL10-6P	ASL10-5/16P		ASC10-01FP	ASC10-ID06BP			
	ASC10-8P	ASC10-3/8P		ASL10-8P	ASL10-3/8P		ASC10-02FP	ASC10-ID09BP			
	ASC10-10P	ASC10-3/8P		ASL10-10P	ASL10-3/8P		ASC10-03FP				
ASC10-12P		ASL10-12P									



Caution

* The model with low sales average may be build to order production. For details, please contact Pisco sales office or sales representative.



Package specification

1 pc. in a bag