

## Select Alarm Unit for Flashing / Alarm Function



LR4~7

Φ40~70

| Model Number | Size (mm) | Mass    |
|--------------|-----------|---------|
| LR4-BW/U     | Φ40       | 0.035kg |
| LR5-BW/U/K   | Φ50       | 0.05kg  |
| LR5-BW+B0960 | Φ50       | 0.05kg  |
| LR6-BW/U     | Φ60       | 0.06kg  |
| LR6-BW+B0960 | Φ60       | 0.06kg  |
| LR7-BW/U/K   | Φ70       | 0.07kg  |

## Select LED Unit(s)



LR4~7

Φ40~70

| Model Number      | Size (mm) | Luminous Color               | Clear Lens | Mass    |
|-------------------|-----------|------------------------------|------------|---------|
| LR4-E-R/Y/G/B/C   | Φ40       | Red/ Amber /Green/Blue/White |            | 0.035kg |
| LR4-E-RZ/YZ/GZ/BZ | Φ40       | Red/ Amber/Green/Blue        | •          | 0.035kg |
| LR5-E-R/Y/G/B/C   | Φ50       | Red/ Amber /Green/Blue/White |            | 0.04kg  |
| LR6-E-R/Y/G/B/C   | Φ60       | Red/ Amber /Green/Blue/White |            | 0.04kg  |
| LR6-E-RZ/YZ/GZ/BZ | Φ60       | Red/ Amber/Green/Blue        | •          | 0.06kg  |
| LR6-E-MZ          | Φ60       | Multi-color 7 colors         | •          | 0.06kg  |
| LR7-E-R/Y/G/B/C   | Φ70       | Red/ Amber /Green/Blue/White |            | 0.065kg |
| LR4-E-R/Y/G/B/C-A | Φ40       | Red/ Amber /Green/Blue/White |            | 0.035kg |

## Select Body Unit

| Model Number     | Size (mm) | Rated Voltage | Mounting                       | Wiring                   | Mass   |
|------------------|-----------|---------------|--------------------------------|--------------------------|--------|
| LR4-02WJNW(U)    | Φ40       | 24V DC        | Direct                         | Cable                    | 0.17kg |
| LR4-M2WJNW       | Φ40       | 100-240V AC   | Direct                         | Cable                    | 0.25kg |
| LR5-01WJNW       | Φ50       | 12V DC        | Direct                         | Cable                    | 0.2kg  |
| LR5-02WJNW       | Φ50       | 24V DC        | Direct                         | Cable                    | 0.2kg  |
| LR6-02WJNW(U)    | Φ60       | 24V DC        | Direct                         | Cable                    | 0.22kg |
| LR6-M2WJNW       | Φ60       | 100-240V AC   | Direct                         | Cable                    | 0.32kg |
| LR7-02WJNW       | Φ70       | 24V DC        | Direct                         | Cable                    | 0.24kg |
| LR5-02WTNW(U)(K) | Φ50       | 24V DC        | Direct                         | Screwless Terminal Block | 0.10kg |
| LR7-02WTNW(U)(K) | Φ70       | 24V DC        | Direct                         | Screwless Terminal Block | 0.15kg |
| LR5-02KTNW(U)(K) | Φ50       | 24V DC        | Dual-mount with knockout holes | Screwless Terminal Block | 0.10kg |
| LR7-02KTNW(U)(K) | Φ70       | 24V DC        | Dual-mount with knockout holes | Screwless Terminal Block | 0.15kg |
| LR4-02LJNW(U)    | Φ40       | 24V DC        | Pole with L-bracket            | Cable                    | 0.46kg |
| LR4-M2LJNW       | Φ40       | 100-240V AC   | Pole with L-bracket            | Cable                    | 0.54kg |
| LR5-01LJNW       | Φ50       | 12V DC        | Pole with L-bracket            | Cable                    | 0.49kg |
| LR5-02LJNW       | Φ50       | 24V DC        | Pole with L-bracket            | Cable                    | 0.49kg |