






















電 流 Current	部品コード Parts code	外 形 Shape	タイプ Type	A 内径 (mm)	B 外径 (mm)	L 全長 (mm)	備 考 Remarks	主な適用トーチ Applicable Torch
180 A用 200 A用	TGN 01208	ネジ径 7/16-14UNC 	小口径タイプ Small dia. Type	13	19	75	—	YT-18CS(B,C,D)□ YT-20CS(B)□ YT-18DS(B)□ YT-20DS(B)□ YT-18ES■ YT-20ES■
	TGN 01311			13	19	65	—	YT-20CF□ YT-20DF□
	TGN 01506	ネジ径 7/16-14UNC 	ストレートタイプ Straight Type	16	19	75	—	YT-18CS(B,C,D)□ YT-20CS(B)□ YT-18DS(B)□ YT-20DS(B)□ YT-18ES■ YT-20ES■
	TGN 01670			16	19	65	—	YT-20CF□ YT-20DF□
200 A用 350 A用 500 A用 (低使用率)	TGN 00044		小口径タイプ Small dia. Type	12	20	73	S1 t 2.0	YT-201CC YT-35DSG3 YT-351CC YT-35EE(M)■ YT-35CE(M)□ YT-35ES(M)■ YT-35CS(M,L)□ YT-35ESG■ YT-35CF(M,L)□ YT-50DE(M,L)□ YT-35CSG□ YT-50CE(M,L)□ YT-35CH(M,L)4 YT-35DE(M)□ YT-35DS(M,L)□ YT-35DF(M,L)□
	TGN 00043		ストレートタイプ Straight Type	16	20	73	S2 t 2.0	
	TGN 00038		16	21	73	S2A 厚肉 t 2.5		
500 A用	TGN 00056		ストレートタイプ Straight Type	19	24	84	S3 t 2.5	YT-501CC(L) YT-50CS(M,L)□ YT-50CSG□ YT-50DS(M,L)□ YT-50DSG3 YT-501CW YT-501CCT6 YT-501CPT4
	TGN 00050			19	25	84	S3A 厚肉 t 3.0	
	TGN 00066		小口径タイプ Small dia. Type	14	24	84	S4 t 2.5	
	TGN 00060			14	25	84	S4A 厚肉 t 3.0	
	TGN 00065		小口径タイプ Small dia. Type	16	24	84	S5 t 2.5	
	TGN 00058			16	25	84	S5A 厚肉 t 3.0	
	TGN 00055		ストレートタイプ Straight Type	19	24	88	S3B	
	TGN 00048			19	25	88	S3C 厚肉 t 3.0	
	TGN 00064		小口径タイプ Small dia. Type	14	24	88	S4B	
	TGN 00063			16	24	88	S5B	
	TGN 00057			16	25	88	S5C 厚肉 t 3.0	
500 A用 600 A用	TGN 01912		ストレートタイプ Straight Type	19	25/30	86	—	YT-501MCZW YT-50CWA1 YT-601CCW
	TGN 00140			20.5	25/30	90	—	YT-CWA50 ○
	TGN 01628		テーパタイプ Taper Type	16	25/30	86	—	YT-501MCZW YT-50CWA1 YT-601CCW