

1 External Pilot, Air Operated Valve

How to Order

VGA342 R - 04

Solenoid valve specifications

R External pilot

Thread type

NH	Rc
F	G
N	NPT
T	NPTF


Port size

04	1/2
06	3/4
10	1

Specifications

Valve type	External pilot, air operated valve	
Type of actuation	Universal porting type	
Fluid	Air	
Operating pressure range	Main pressure	-101.2 kPa to 0.9 MPa
	Pilot pressure	Equivalent to main pressure (Min. 0.2 MPa or more)
	External pilot	Equivalent to pilot pressure
Ambient and fluid temperature	-10 to 50°C (No freezing.)	
Weight	1.2 kg	

Symbol



Dimensions

