

Fan Type Ionizer

IZF21/31 Series



How to Order

IZF **21** - - **B**

Model

Symbol	Max. air flow
21	1.8 m ³ /min
31	4.4 m ³ /min

Input/Output specifications

Nil	NPN input/output
P	PNP input/output

Power supply cable, AC adapter

Nil	With power supply cable (3 m)
Z	With power supply cable (10 m)
Q	With AC adapter (with AC cord)
R	With AC adapter (without AC cord)
N	None

Filter

Nil	None
U	With filter*

* Filter + Filter holder

Automatic cleaning unit, Louver

Nil	None
S	With automatic cleaning unit
W	With adjustable louver
Y	With automatic cleaning unit + adjustable louver

Bracket

Nil	None
B	With bracket