

**How to Order**

**Tubing connection**

**LQ3 E 11 -** □

**Fitting type**

Symbol	Type
<b>E</b>	Union elbow
<b>T</b>	Union tee
<b>P</b>	Panel mount union
<b>U</b>	Union

**Nut material, packaging**

Symbol	Nut material	Packaging
<b>NH</b>	PFA	Clean packaging equivalent to Class M3.5
<b>1</b>	PFA	Standard packaging equivalent to Class M5.5
<b>2</b>	PVDF	Clean packaging equivalent to Class M3.5
<b>3</b>	PVDF	Standard packaging equivalent to Class M5.5

\* LQ3□8A: Nut material PVDF is not available.

**Size combination**

Size	No.	Applicable tubing size (mm)
<b>1</b>	<b>1</b>	4 x 3
<b>1</b>	<b>2</b>	3 x 2
<b>2</b>	<b>1</b>	6 x 4
<b>3</b>	<b>1</b>	10 x 8
<b>3</b>	<b>2</b>	8 x 6
<b>4</b>	<b>1</b>	12 x 10
<b>5</b>	<b>1</b>	19 x 16
<b>6</b>	<b>1</b>	25 x 22

Size	Symbol	Applicable tubing size (inch)
<b>1</b>	<b>A</b>	1/8" x 0.086"
<b>2</b>	<b>A</b>	1/4" x 5/32"
<b>3</b>	<b>A</b>	3/8" x 1/4"
<b>4</b>	<b>A</b>	1/2" x 3/8"
<b>5</b>	<b>A</b>	3/4" x 5/8"
<b>6</b>	<b>A</b>	1" x 7/8"
<b>7*</b>	<b>A*</b>	1 1/4" x 1.1"
<b>8*</b>	<b>A*</b>	1 1/2" x 1.33"

Note) For details of the applicable tubing sizes, refer to page 945.

\* P: Without panel mounting

<b>LVC</b>
<b>LVA</b>
<b>LVB</b>
<b>LVD</b>
<b>LVE</b>
<b>LVP</b>
<b>LWV</b>
<b>LQ1</b>
<b>LQ3</b>
<b>LVN</b>
<b>LQHB</b>
<b>TL</b>
<b>TIL</b>
<b>TLM</b>
<b>TILM</b>
<b>TD</b>
<b>TID</b>
<b>TH</b>
<b>TIH</b>