



TOGGLE CLAMP (Vertical Handle Type) **TDV650F**



Item No.	Base type	N.W.(g)
TDV650F	Flange	648

- Max. holding capacity : 3.4kN
- Clamp arm moving angle : 105°
- Handle operation angle : 58°
- Supporting pin : stainless steel

TDS10F



Item No.	Base type	N.W.(g)
TDS10F	Flange	15

- Max. holding capacity : 0.2kN
- Clamp arm moving angle : 50°
- Handle operation angle : 80°
- Supporting pin : stainless steel

TD09(F·S)·STD09F



Item No.	Base type	N.W.(g)
TD09F	Flange	42
TD09S	Straight	42
STD09F	Flange/stainless steel	42

- Max. holding capacity : 0.3kN
- Clamp arm moving angle : 80°
- Handle operation angle : 88°
- Supporting pin : stainless steel

TDA40(F·S)·STDA40(F·S)



Item No.	Base type	N.W.(g)
TDA40F	Flange	218
TDA40S	Straight	218
STDA40F	Flange/stainless steel	218
STDA40S	Straight/stainless steel	218

- Max. holding capacity : 1.0kN
- Clamp arm moving angle : 95°
- Handle operation angle : 65°
- Supporting pin : stainless steel

