

Color Type

Color code	Top cover color / Material	Base color / Material
BCAP[G]	White gray / ABS	White gray / ABS
BCAP[T]	Transparent / Polycarbonate	White gray / ABS
BCPC[S]	Light gray / Polycarbonate	Light gray / Glass fiber filled polycarbonate

■ Please suffix color code at the end of the product number.



BCAP Product no. / Dimensions

Product no.	W	D	H	Weight (g)	
				G	T
BCAP091207□	90	120	70	196	204
BCAP091208□	90	120	85	212	221
BCAP101507□	100	150	70	272	281
BCAP101508□	100	150	85	291	300
BCAP112107□	110	210	75	359	378
BCAP112110□	110	210	100	422	420
BCAP112607□	110	260	75	431	446
BCAP112610□	110	260	100.5	484	500
BCAP131508□	135	155	85	356	357
BCAP131808□	135	185	85.5	381	410
BCAP131810□	135	185	100.5	396	402
BCAP151509□	150	150	90	343	353
BCAP151512□	150	150	120.5	411	425
BCAP162110□	160	210	100	468	486
BCAP162113□	160	210	130	517	537
BCAP162610□	160	260	100	577	601
BCAP162613□	160	260	130	673	701
NEW BCAP172210□	170	220	105	545	581
BCAP172711□	170	270	110.5	670	680
BCAP192810□	190	280	100.5	722	746
BCAP192814□	190	280	141	877	901
NEW BCAP203013□N	200	300	130	921	954
NEW BCAP203015□N	200	300	150	989	1,022
NEW BCAP203018□N	200	300	180	1,110	1,143
BCAP212110□	210	210	100	630	656
BCAP212113□	210	210	130	704	726
NEW BCAP253515□N	250	350	150	1,278	1,320
NEW BCAP253518□N	250	350	180	1,415	1,456
BCAP282813□	280	280	130.5	1,167	1,200
BCAP283813□	280	380	130	1,455	1,512
BCAP303015□	300	300	151	1,339	1,418
BCAP303018□	300	300	181	1,495	1,576
BCAP304012□	300	400	120	1,508	1,575
BCAP304015□	300	400	150	1,563	1,675
BCAP304018□	300	400	181	1,719	1,853
BCAP353515□	350	350	150	1,693	1,764
BCAP353518□	350	350	181	1,845	1,906
BCAP354512□	350	450	120	2,068	2,167
BCAP354516□	350	450	160	2,382	2,514
BCAP354520□	350	450	201	2,646	2,794
BCAP405016□	400	500	160	2,660	2,839
BCAP405020□	400	500	201	3,119	3,232
BCAP406018□	400	600	181	3,542	3,652
BCAP406023□	400	600	231	3,870	4,044
BCAP506018□	530	630	185	5,438	5,611
BCAP506025□	530	630	255	6,078	6,273
BCAP507018G	530	730	188	6,241	—
BCAP507025G	530	730	255	6,911	—
BCAP608018G	630	830	188	8,131	—
BCAP608028G	630	830	288	9,570	—

■ BCAP507018, 507025, 608018, and 608028 models are only available as G color type.

BCPC Product no. / Dimensions

Product no.	W	D	H	Weight (g)	
				G	T
BCPC091207S	90	120	70	226	—
BCPC091208S	90	120	85	247	—
BCPC101507S	100	150	70	312	—
BCPC101508S	100	150	85	336	—
BCPC112107S	110	210	75	420	—
BCPC112110S	110	210	100	473	—
BCPC112607S	110	260	75	493	—
BCPC112610S	110	260	100.5	569	—
BCPC131508S	135	155	85	406	—
BCPC131808S	135	185	85.5	452	—
BCPC131810S	135	185	100.5	448	—
BCPC151509S	150	150	90	395	—
BCPC151512S	150	150	120.5	482	—
BCPC162110S	160	210	100	556	—
BCPC162113S	160	210	130	611	—
BCPC162610S	160	260	100	671	—
BCPC162613S	160	260	130	779	—
NEW BCPC172210S	170	220	105	642	—
BCPC172711S	170	270	110.5	775	—
BCPC192810S	190	280	100.5	858	—
BCPC192814S	190	280	141	1,028	—
NEW BCPC203013SN	200	300	130	1,070	—
NEW BCPC203015SN	200	300	150	1,150	—
NEW BCPC203018SN	200	300	180	1,295	—
BCPC212110S	210	210	100	742	—
BCPC212113S	210	210	130	827	—
NEW BCPC253515SN	250	350	150	1,485	—
NEW BCPC253518SN	250	350	180	1,648	—
BCPC282813S	280	280	130.5	1,371	—
BCPC283813S	280	380	130	1,695	—
BCPC303015S	300	300	151	1,610	—
BCPC303018S	300	300	181	1,760	—
BCPC304012S	300	400	120	1,846	—
BCPC304015S	300	400	150	1,862	—
BCPC304018S	300	400	181	2,030	—
BCPC353515S	350	350	150	2,045	—
BCPC353518S	350	350	181	2,142	—
BCPC354512S	350	450	120	2,397	—
BCPC354516S	350	450	160	2,826	—
BCPC354520S	350	450	201	3,151	—
BCPC405016S	400	500	160	3,188	—
BCPC405020S	400	500	201	3,811	—
BCPC406018S	400	600	181	4,153	—
BCPC406023S	400	600	231	4,637	—
BCPC506018S	530	630	185	6,305	—
BCPC506025S	530	630	255	7,213	—
BCPC507018S	530	730	188	7,410	—
BCPC507025S	530	730	255	8,200	—
BCPC608018S	630	830	188	9,820	—
BCPC608028S	630	830	288	11,550	—

■ Refer to page 311 ~ 314 for detailed dimensions.

Accessories (Optional parts)



Mounting plate BMP series
See page 317 ~ 319



Mounting bracket CK • BFL series
See page 320



Pole mounting bracket SSK series
See page 321 ~ 322



Cable gland
See page 333 ~ 340



Ventilation parts
See page 325 ~ 328