

Grip Tapes

The number next to the logo mark indicates items in stock for each brand.

Hammers • Punches

Single-Ended Hammers

Double-Ended Hammers

Combination Hammers

Shock-Less Hammers

Resin Hammers • Rubber Hammers

Nonferrous Hammers

Stainless Steel Hammers

Wood Hammers

Stone Hammers

Welding Hammers

Sheet Metal Hammers

Claw Hammers

Centering Hammers

Hammers for Woodwork

Hammers for Electric Work

Test Hammers

Wedges

Grip Tapes

Bars

Chisels

Stamps

Date Marks

Industrial Stamps

Punches

TRUSCO
Stock 38,650 Items

Grip Stopper (oil resistant type)



TGP-970-OR (orange)

- Features**
- Easily wrapped on your tool, control lever, etc. and can provide anti-slip effect.
 - With the very thin thickness of 0.5mm, it does not make you feel uncomfortable when you grasp it.
 - **Excellent in oil resistance because it uses Nitrile rubber.**
- Specs**
- With end tape for rolling up
- Materials**
- Nitrile Rubber, Acrylic Adhesive
- Origin**
- Japan



Order Unit: 1 Roll

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Color	Total Length (mm)	Width (mm)	Thickness (mm)	SPQ (roll)	Weight (g)
384-1359	TGP-970-BK	¥537	¥580	Black	970	30	0.5	10	23
384-1375	TGP-970-OR	¥537	¥580	Orange	970	30	0.5	10	23
384-1367	TGP-970-GN	¥537	¥580	Green	970	30	0.5	10	23
384-1383	TGP-970-Y	¥537	¥580	Yellow	970	30	0.5	10	23

TRUSCO NAKAYAMA CORPORATION

Contact us: 0120-509-849 <http://www.orange-book.com/>

OH
Stock 688 Items

Grip Tape (shock absorbent type)



GTS-BK (black)

- Features**
- Polyurethane tape with a moist feeling gives excellent grip power.
 - Prevents vibration and impact from being transmitted to the hands and reduces fatigue.
 - Micro holes on the tape surface absorb sweat quickly and prevent slippage.
- Materials**
- Polyurethane (tape/sponge)
- Origin**
- Japan

OH
Stock 688 Items

Grip Tape (thin type)




GTU-BK (black)

- Features**
- Polyurethane tape with a moist feeling gives excellent grip power.
 - Prevents vibration and impact from being transmitted to the hands and reduces fatigue.
- Materials**
- Polyurethane
- Origin**
- Japan



Example



Order Unit: 1 Piece

O.H.INDUSTRIAL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Width (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
395-8728	GTS-BK	¥490	¥530	Black	1050	26	0.5	5	10
395-8736	GTS-BL	¥490	¥530	Blue	1050	26	0.5	5	10
395-8744	GTS-GN	¥490	¥530	Green	1050	26	0.5	5	10

URL <http://www.ohnet.co.jp/>



Order Unit: 1 Piece

O.H.INDUSTRIAL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Width (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
402-9631	GTU-BK	¥361	¥390	Black	1050	26	0.5	5	8
402-9640	GTU-O	¥361	¥390	Orange	1050	26	0.5	5	8
402-9658	GTU-R	¥361	¥390	Red	1050	26	0.5	5	8

URL <http://www.ohnet.co.jp/>


OH
Stock 688 Items

Grip Tape (thin checkered type)



GTC-S (silver)

- Features**
- Polyurethane tape with a moist feeling gives excellent grip power.
 - Prevents vibration and impact from being transmitted to the hands and reduces fatigue.
 - A checkered pattern to express individuality.
- Materials**
- Polyurethane
- Origin**
- Japan



Order Unit: 1 Piece

O.H.INDUSTRIAL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Width (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
449-1971	GTC-BK	¥463	¥500	Black	1050	26	0.5	5	13
449-1980	GTC-BL	¥463	¥500	Blue	1050	26	0.5	5	13
449-1998	GTC-S	¥463	¥500	Silver	1050	26	0.5	5	13

URL <http://www.ohnet.co.jp/>

OHSO
Stock 91 Items

"G-TAPE Super Long EX Size"



033906 (black)

- Features**
- A wet grip tape with a superior sweat-absorbent and quick-drying which prevent slippage.
 - 120cm and compatible to lengthy product.
 - Durable and excellent in cost performance as less frequent exchanges required.
- Materials**
- Polyurethane
- Origin**
- Japan



Order Unit: 1 Piece

SUSA MANUFACTURING.CO.LTD

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Total Length (mm)	Width (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
818-4306	033906	¥1,435	¥1,550	Black	1200	31	0.6	6	30
818-4307	033913	¥1,435	¥1,550	Red	1200	31	0.6	6	30
818-4308	033951	¥1,435	¥1,550	White	1200	31	0.6	6	30
818-4309	039968	¥1,435	¥1,550	Yellow	1200	31	0.6	6	30

Contact us: 0256-46-4834 <http://www.tonkachi.com/>