

Ball-Point Hexagonal Wrenches

Stock 1,057 Items

4-725

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

Ball-Point Hexagonal Wrench



- Length Features**
- Flat corners at the tip of the hexagonal bar are chamfered equally on each side.
 - Compared with popular products, high torque, durability and wear resistance are outstandingly excellent.
 - Easier insertion in the hexagon socket hole and moreover the chamfer angle is designed to be in close contact with "corner edge" of the hexagon hole base.
- Materials**
- Chromium molybdenum steel SNCM/V (1.5 to 10mm)
 - Chrome Vanadium Steel CR-V (12 to 14mm)
- Origin**
- Taiwan

Order Unit: 1 Piece (Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
445-3760	TXB-15	¥ 259	¥ 280	1.5	14	77	50	1.4
445-3778	TXB-20	¥ 259	¥ 280	2.0	16	83	50	2.7
445-3786	TXB-25	¥ 269	¥ 290	2.5	18	90	50	4.7
445-3794	TXB-30	¥ 295	¥ 318	3.0	20	98	50	7.3
445-3808	TXB-40	¥ 306	¥ 330	4.0	25	106	50	15.0
445-3816	TXB-50	¥ 336	¥ 363	5.0	28	118	50	25.0
445-3824	TXB-60	¥ 370	¥ 400	6.0	32	137	40	42.0
445-3832	TXB-80	¥ 500	¥ 540	8.0	36	156	30	85.0
445-3841	TXB-100	¥ 724	¥ 782	10.0	40	170	20	146.0
445-3859	TXB-120	¥ 1,157	¥ 1,250	12.0	45	207	10	250.0
445-3867	TXB-140	¥ 1,537	¥ 1,660	14.0	56	230	10	386.0

Set Accessories • Holder

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
279-4799	TXB-9S	¥ 3,157	¥ 3,410	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	9	6	362

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Ball-Point Hexagonal Wrench



- Features**
- Surface treatment is black dye processing.
 - The hardness is HRC52 to 56.
- Materials**
- Chrome Vanadium Steel (Cr-V)
- Origin**
- Taiwan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
389-6200	TTBR-15	¥ 120	¥ 130	1.5	14	77	50	1.40
389-6218	TTBR-20	¥ 130	¥ 140	2.0	16	83	50	2.72
389-6226	TTBR-25	¥ 139	¥ 150	2.5	20	98	50	4.63
389-6234	TTBR-30	¥ 166	¥ 180	3.0	20	98	50	7.30
389-6242	TTBR-40	¥ 176	¥ 190	4.0	25	106	50	14.30
389-6251	TTBR-45	¥ 185	¥ 200	4.5	26	112	50	19.20
389-6269	TTBR-50	¥ 204	¥ 220	5.0	28	118	50	25.10
389-6277	TTBR-55	¥ 213	¥ 230	5.5	30	128	50	32.90
389-6285	TTBR-60	¥ 231	¥ 250	6.0	32	137	40	41.90
389-6293	TTBR-70	¥ 269	¥ 290	7.0	34	147	30	61.20
389-6307	TTBR-80	¥ 324	¥ 350	8.0	36	156	30	84.90
389-6315	TTBR-100	¥ 463	¥ 500	10.0	40	170	20	145.44
389-6323	TTBR-120	¥ 694	¥ 750	12.0	45	207	10	251.00
389-6331	TTBR-140	¥ 1,018	¥ 1,100	14.0	56	230	10	385.00
389-6340	TTBR-170	¥ 1,805	¥ 1,950	17.0	63	250	5	623.00
389-6358	TTBR-190	¥ 2,444	¥ 2,640	19.0	70	280	5	877.00

Set Accessories • Holder

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
366-8827	TBR-9S	¥ 2,343	¥ 2,530	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	9	6	385
366-8819	TBR-12S	¥ 2,851	¥ 3,080	1.5, 2, 2.5, 3, 4, 4.5, 5, 5.5, 6, 7, 8, 10	12	6	501

Set Accessories • Pouch

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (kg/set)
488-7573	TBR-16S	¥ 8,979	¥ 9,700	1.5, 2, 2.5, 3, 4, 4.5, 5, 5.5, 6, 7, 8, 10, 12, 14, 17, 19	16	1	3.0

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Ball-Point Hexagonal Wrench Set



TBRI20S

- Features**
- Newly developed compact tool case that open and close 360° with milli size, inch size ball point hexagonal wrench all comes in a 10 piece set each.
- Materials**
- Chrome Vanadium Steel (Cr-V)
- Origin**
- Taiwan

SPQ: 20 Sets

Order Unit: 1 Set TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Weight (g/set)
818-3234	TBRI20S	¥ 4,814	¥ 5,200	1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10, 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	974

Contact us: 0120-509-849 <http://www.orange-book.com/>

Screwdrivers Hexagonal Wrenches

Grip Screwdrivers

Screwdrivers with Plastic Handle

Stubby Screwdrivers

Screwdrivers with Wood Handle

Precision Screwdrivers

Electric Detection Screwdrivers

Interchangeable Screwdrivers

Ratchet Screwdrivers

Offset Ratchet Screwdrivers

Socket Screwdrivers

Impact Drivers (Manual Type)

Hexagon Driver

Hex Lobe Screwdrivers

Special-Purpose Screwdrivers

Ball-Point Hexagonal Wrenches

Hexagonal Wrenches

Hex Lobe Wrenches