

>>> For cylinder locks, see p. 2-876 to 884

The number next to the logo mark indicates items in stock for each brand.

Steel
Tool
BoxesStainless
Tool
BoxesPartition
BoxesPlastic
Tool
BoxesSystem
BoxesAttache
CasesParts
CasesTool
BoxesIn-Car
Tool
BoxesAluminum
CasesProtector
Tool
CasesStock
38,650
Items

"Protector Tool Case"



- Features** • A resin tool case with high durability and sealability, so it is optimum for storing and transporting precision machinery.
- Specs** • Waterproof Type
• Cylinder Lock Attachable (sold separately)
- Materials** • Main Body: Polypropylene (PP)
• Cushion: Urethane
- Accessories** • Buffer Urethane
• Shoulder belt (L/XL size only)
- Origin** • China



TAK-13L (black)



TAK13RE-L (red)



TAK13OD-L (OD)



TAK13OR-L (orange)

Item No.	Cylinder Lock Hole Diameter (mm)
TAK-13L TAK13RE-L TAK13OD-L TAK13OR-L	6.5

Order Unit: 1 Piece

(Price revision date: Apr, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Outer Dimension (mm) W x D x H	Effective Inner Dimension (mm) W x D x H	Load Capacity (kg)	SPQ (piece)	Weight (kg)
328-6282	TAK-13L	¥9,442	¥10,200	Black	430 x 380 x 154	395 x 320 x 143	50	3	3.1
389-5297	TAK13RE-L	¥9,442	¥10,200	Red	430 x 380 x 154	395 x 320 x 143	50	3	3.1
389-5335	TAK13OD-L	¥9,442	¥10,200	OD	430 x 380 x 154	395 x 320 x 143	50	3	3.1
389-5378	TAK13OR-L	¥9,442	¥10,200	Orange	430 x 380 x 154	395 x 320 x 143	50	3	3.1



TAK-13XL (black)



TAK13RE-XL (red)



TAK13OD-XL (OD)



TAK13OR-XL (orange)

Item No.	Cylinder Lock Hole Diameter (mm)
TAK-13XL TAK13RE-XL TAK13OD-XL TAK13OR-XL	6.5

Order Unit: 1 Piece

(Price revision date: Apr, 2016)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Color	Outer Dimension (mm) W x D x H	Effective Inner Dimension (mm) W x D x H	Load Capacity (kg)	SPQ (piece)	Weight (kg)
328-6291	TAK-13XL	¥12,775	¥13,800	Black	515 x 415 x 200	485 x 355 x 186	50	2	4.3
389-5301	TAK13RE-XL	¥12,775	¥13,800	Red	515 x 415 x 200	485 x 355 x 186	50	2	4.3
389-5343	TAK13OD-XL	¥12,775	¥13,800	OD	515 x 415 x 200	485 x 355 x 186	50	2	4.3
389-5386	TAK13OR-XL	¥12,775	¥13,800	Orange	515 x 415 x 200	485 x 355 x 186	50	2	4.3



TAK13K Series (buffer urethane)

Buffer Urethane

- Features** • Cushioning material of corrugated die urethane (soft) and urethane with cut (hardness) firmly guards stored items from impact.
- Urethane with cut possible to easily make a drawn shape according to the stored items.
- Specs** • TAK13K-ML only urethane on the main body side (break with/without) There are 2 types

Item No.	Lid Corrugated Die Urethane (sheet)	Main Body Side Corrugated Die Type Urethane (sheet)	Urethane with Cut on Main Body Side (sheet)
TAK13K-S	1	1	1
TAK13K-SM	1	0	3
TAK13K-M	1	1	2
TAK13K-ML	1	0	3
TAK13K-L	1	1	2
TAK13K-XL	1	1	2

(Price revision date: Apr, 2016)

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Lid Corrugated Die Urethane Size W x D x H (mm)	Main Body Side Corrugated Die Type Urethane Size W x D x H (mm)	Urethane with Cut on Main Body Side W x D x H (mm)	SPQ (set)	Weight (g/set)
389-5416	TAK13K-S	¥ 565	¥ 610	182 x 120 x 10	188 x 124 x 43	188 x 124 x 22	10	31.0
835-9343	TAK13K-SM	¥ 926	¥1,000	150 x 215 x 20	-	150 x 215 x 33(2 sheets)/150 x 215 x 5(not notch)	16	70.5
389-5424	TAK13K-M	¥ 796	¥ 860	297 x 217 x 25	297 x 217 x 25	299 x 219 x 22	3	106.0
818-9502	TAK13K-ML	¥2,129	¥2,300	380 x 265 x 45	-	370 x 260 x 10(no notch x 1 sheet)/380 x 270 x 42(2 sheets)	4	248.0
389-5432	TAK13K-L	¥1,833	¥1,980	400 x 323 x 35	398 x 323 x 40	398 x 323 x 32	2	329.0
389-5441	TAK13K-XL	¥2,278	¥2,460	484 x 355 x 70	478 x 355 x 18	470 x 345 x 38	3	483.0

Contact us:0120-509-849 <http://www.orange-book.com/>