

Polishing Belts

The number next to the logo mark indicates items in stock for each brand.

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

TRUSCO **Stock 38,650 Items**

Endless Belt

Com Drawing



TEB100-A Series

Estimated Unit Price per Piece
¥381 to ¥462

- Features**
- A belt for belt sander 100 x 915 size which is widely used.
 - Can be used widely from heavy grinding to burring.
 - Can be used with wet type dry type.
 - Can be used for both steel and woodworking.
- Use**
- Various burring, surface treatment.
 - Tool repair, removal of rough scratches.
 - Grinding and polishing of metal parts.
- Materials**
- Abrasive: Alundum Abrasive Grain (A)
- Origin**
- Base Material: Cloth
 - Japan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	W x L (mm)	Q'ty Per Box (piece)	SPQ (box)	Weight (kg/box)
471-9735	TEB100-A40	¥4,617	¥5,700	40	100 x 915	10	10	1600
471-9743	TEB100-A60	¥4,293	¥5,300	60	100 x 915	10	10	1200
471-9751	TEB100-A80	¥4,050	¥5,000	80	100 x 915	10	10	1100
471-9760	TEB100-A100	¥3,807	¥4,700	100	100 x 915	10	10	1000
471-9778	TEB100-A120	¥3,807	¥4,700	120	100 x 915	10	10	900
471-9786	TEB100-A180	¥3,807	¥4,700	180	100 x 915	10	10	900
471-9794	TEB100-A240	¥3,807	¥4,700	240	100 x 915	10	10	900
471-9808	TEB100-A320	¥3,807	¥4,700	320	100 x 915	10	10	900
471-9816	TEB100-A400	¥3,807	¥4,700	400	100 x 915	10	10	900

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Zirconia Endless Belt

Com Eco Chemical Content Inspection

Com Drawing SDS



TEB100-Z Series

Estimated Unit Price per Piece
¥442 to ¥567

- Features**
- Since zirconia abrasive grain is used for abrasants, sharpness is sharp, and excellent grinding force is demonstrated.
 - Double coat processing of heat dissipating agent, generation of polishing heat is less, burning is reduced.
 - Durability is improved because strong fiber is used for the base fabric textile.
- Use**
- Optimum for grinding and polishing of stainless steel materials, steel materials, etc.
 - Possible to wide range from general polishing to heavy grinding.
 - Burring of metallic working tools, cutleries etc., bead removal, removal of black layer, etc.
- Materials**
- Abrasive: Zirconia Abrasive Grain (Z)
- Origin**
- Japan

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	W x L (mm)	Q'ty Per Box (piece)	SPQ (box)	Weight (kg/box)
299-7231	TEB100-Z40	¥5,670	¥7,000	40	100 x 915	10	10	1.9
299-7240	TEB100-Z60	¥5,103	¥6,300	60	100 x 915	10	10	1.6
299-7258	TEB100-Z80	¥4,820	¥5,950	80	100 x 915	10	10	1.4
299-7266	TEB100-Z100	¥4,415	¥5,450	100	100 x 915	10	10	1.3
299-7274	TEB100-Z120	¥4,415	¥5,450	120	100 x 915	10	10	1.2

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

"FB Fine Belt"

Com Eco Chemical Content Inspection

Com Drawing SDS



TFB-100915

- Features**
- With rich elasticity, smooth finishing can be conducted without excessively cutting the base.
 - Due to its nice fit that enables smooth polishing with little vibrations when polishing, ease of use has been improved.
 - Ideal for fine burr removal and chamfering.
 - Ideal for narrow spaces on curved surfaces and uneven surfaces.
 - Compared to the super fine belt, it has grinding performance which makes it suitable for polishing stainless steel.
- Use**
- Burr removal and grain blurring after machine processing.
 - Hairline processing of stainless steel products.
 - Rust removal, peel off paint film.
- Materials**
- Abrasive: Alundum Abrasive Grain (A)
 - Nylon non woven fabric
- Origin**
- Japan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Color	W x L (mm)	SPQ (piece)	Weight (g)
299-6898	TFB-100915-60	¥2,633	¥3,250	60	Black	100 x 915	1	300
299-6901	TFB-100915-80	¥2,633	¥3,250	80	Purple	100 x 915	1	300
299-6910	TFB-100915-120	¥2,633	¥3,250	120	Red	100 x 915	1	300
299-6928	TFB-100915-220	¥2,633	¥3,250	220	Red	100 x 915	1	300
299-6936	TFB-100915-320	¥2,633	¥3,250	320	Brown	100 x 915	1	300

Contact us: 0120-509-849 <http://www.orange-book.com/>

