



Stock 38,650 Items

Twist Cup Brush for Electric Tool



TCB-75A (steel wire)



TCB-75AS (stainless steel)

- Features**
- The shape of the wire material of the brush is rope-like and the tip is radially frayed, making it suitable for powerful polishing of larger areas.
- Use**
- For Flat Surface Polishing
 - Processing before and after the welding work, burring, surface treatment, removal of tough rust remover, paint removal and oxidized scale removal, etc.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Electric Tools
- Origin**
- Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
827-7134	TCB-75A	¥2,962	¥3,200	75	0.35	Steel Wire	M10 (P1.5)	12000	30	260
820-6429	TCB-75AS	¥4,184	¥4,520	75	0.35	Stainless Steel	M10 (P1.5)	12000	30	260

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Twist Cup Brush for Electric Tool



TCBC-75 (steel wire)



TCBC-75S (stainless steel)

- Features**
- The shape of the wire rod of the brush is rope-like and the tip is cut so that it produces a powerful polishing force.
 - High-quality raw material made in JAPAN is used for wire rod material.
- Use**
- For Flat Surface Polishing
 - Processing before and after the welding work, burring, surface treatment, removal of tough rust remover, paint removal and oxidized scale removal, etc.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Electric Tools
- Origin**
- Korea

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
445-8273	TCBC-75	¥3,610	¥3,900	75	0.5	Steel Wire	M10 (P1.5)	12000	10	320
445-8281	TCBC-75S	¥5,091	¥5,500	75	0.5	Stainless Steel	M10 (P1.5)	12000	10	320

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Bevel Brush for Electric Tool



GBB-85 (brass plating steel wire)



GBB-85S (stainless steel)

- Features**
- Burring, rust remover, demonstrate its power in paint removal.
 - Optimum for fine small burring after cutting and grinding.
- Use**
- For curved surface polishing
 - Rust prevention and polishing of iron and steel/non-ferrous metals, burring of welding, paint removal, base polishing, edge finishing of rubber production process, surface processing.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Electric Tools
- Origin**
- Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
227-8162	GBB-85	¥1,407	¥1,520	85	0.27	Brass Plating Steel Wire	M10 (P1.5)	12000	10	180
227-8171	GBB-85S	¥3,333	¥3,600	85	0.30	Stainless Steel	M10 (P1.5)	12000	10	180

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Bevel Brush for Air Tool



GBB-85AC (brass plating steel wire)



GBB-85AS (stainless steel)

- Features**
- Since brushes are not abrasives like grinding wheels and coated whetstone abrasive piece, they do not scrape the products themselves, they are optimum for removing dirt and deposits on the surface.
- Use**
- For curved surface polishing
 - Rust remover/oxide film removal after welding.
 - Paint removal and ground processing.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Pneumatic Tools
- Origin**
- Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Hole Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
352-0692	GBB-85AC	¥1,342	¥1,450	85	0.27	Brass Plating Steel Wire	16	13600	20	160
352-0684	GBB-85AS	¥3,194	¥3,450	85	0.30	Stainless Steel	16	13600	20	160

Contact us:0120-509-849 <http://www.orange-book.com/>