



Premium Platinum that exceeds type A

Pursue "Strength".

The amount of flame resistant fiber used is approx. 1.5 times compared to general type A spatter sheets. (compared to our company's products)

Even without coating, it is further coated on both sides of the fabric which passed the A type.

Both A side specification can be used for both white and pink color surfaces.

Premium test (our own test)



	Thickness of Steel Plate (mm)	Cutting Speed (mm/min)	Oxygen Pressure (kg/cm ²)	Acetylene Pressure (kg/cm ²)
JIS A1323 Type A	9.0	500	2.5	0.25
Premium Test	19.0	500	5.0	0.5

YOSHINO

Stock
184 Items

Spatter Sheet "Premium Platinum" (double side coating)



Features • Spatter sheet which has resisted the test with the stricter conditions than Class A (compared to our company's products).

Use • Excellent tensile strength, it is flexible and easy-to-handle, even though with its thickness.
• Non-asbestos/non-ceramic safe product, also containing no fibers that induce skin irritation.

Specs • As a welding spark and slag receiving sheet, fire proof curtain, and curing sheet.
• JIS A 1323 Class A Passing No. 09A0154 • (foundation) Japan Fire Retardant Association Flame Retardant Performance Test compliant No. CO090006 • Thickness: Approx. 1.3mm

Materials • Flame Resistant Fiber Fabrics • Silicone double-sided processing (front: white/back: pink color)

Origin • Japan

Order Unit: 1 Sheet

YOSHINO LIMITED.

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Type	Number of Eyelets	Eyelet Pitch (mm)		W x L (mm)	SPQ (sheet)	Weight (kg)
						A	B			
351-7454	YS-PP-1	¥ 6,804	¥ 6,300	No. 1	4	880	880	920 x 920	10	0.9
351-7462	YS-PP-2	¥ 13,608	¥ 12,600	No. 2	12	440	470	920 x 1920	10	1.8
351-7471	YS-PP-4	¥ 27,216	¥ 25,200	No. 4	16	470	470	1920 x 1920	5	3.6
351-7489	YS-PP-6	¥ 40,824	¥ 37,800	No. 6	20	470	480	1920 x 2920	5	5.4
351-7497	YS-PPR-S	¥ 113,400	¥ 105,000	Roll	-	-	-	1000 x 20m	1	18.0
351-7501	YS-PPR-W	¥ 226,800	¥ 210,000	Roll	-	-	-	2000 x 20m	1	36.0

Sell by Piece Type Features • You can order with your preferred length (m unit).

Order Unit: 1m | Factory direct | Shipping not included

Order Code	Item No.	Price (per m)	MSRP (per m)	Type	Number of Eyelets	Eyelet Pitch (mm)		W x L (mm)	Weight (kg/m)
						A	B		
★467-4111	YS-PPR-CUT-S	¥ 6,264	¥ 5,800	Cut	-	-	-	1000 x In meter unit	0.9
★467-4120	YS-PPR-CUT-W	¥ 12,528	¥ 11,600	Cut	-	-	-	2000 x In meter unit	1.8

Contact us: 050-3803-2900 <http://www.yoshino-limited.co.jp/>

TRUSCO

Stock
38,650 Items

Sputter Sheet "Super" (double coated)



TSP-2SP

Features • Lightweight type coated with special silicone on both sides of glass fiber.

Use • A type to repel sparks, slag. • Safe product with no asbestos/ceramic.
• As welding and cutting spark receiving sheet, welding spark shielding curtain.
• As heat resistant curtain, high temperature valve cover material.

Specs • JIS A 1323 Class B passing No. 05A3881 • Thickness: 0.38mm

Materials • Base Fabric: 100% Glass Fiber • Coating: Special Silicone Resin Origin • Japan

Order Unit: 1 Sheet | Blue | Factory direct | Shipping not included | (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Type	Number of Eyelets	Eyelet Pitch (mm)		W x L (mm)	SPQ (sheet)	Weight (kg)
						A	B			
300-6484	TSP-1SP	¥ 5,638	¥ 6,090	No. 1	4	880	880	920 x 920	15	0.6
300-6492	TSP-2SP	¥ 11,275	¥ 12,180	No. 2	12	440	470	920 x 1920	8	1.2
300-6506	TSP-4SP	¥ 22,550	¥ 24,360	No. 4	16	470	470	1920 x 1920	4	2.4
300-6514	TSP-6SP	¥ 33,826	¥ 36,540	No. 6	20	470	480	1920 x 2920	3	3.6
300-6522	TSP-RSP	¥ 128,498	¥ 138,810	Roll	-	-	-	1000 x 30m	1	16.0
★837-1266	TSP-RSP-W	¥ 256,978	¥ 277,600	Roll	-	-	-	2000 x 30m	1	32.0

Sell by Piece Type Features • You can order with your preferred length (m unit).

Order Unit: 1m | Factory direct | Shipping not included

Order Code	Item No.	Price (per m)	MSRP (per m)	Type	Number of Eyelets	Eyelet Pitch (mm)		W x L (mm)	Weight (kg/m)
						A	B		
★402-7329	TSP-RSP-CUT	¥ 4,860	¥ 5,250	Cut	-	-	-	1000 x In meter unit	0.6
★402-7337	TSP-RSP-CUT-W	¥ 9,720	¥ 10,500	Cut	-	-	-	2000 x In meter unit	1.2

Contact us: 0120-509-849 <http://www.orange-book.com/>

Warning
• Depending on the constitution, there is a possibility of itching and rough skin.