













Type	Gate			Gate			Gate			Globe			Globe			
																
Fig	150-BSR-NR-NPT<UL1R1>			150-BSRU-NR-NPT<UC8R1>			300-BSRU-NR-NPT<UC8R1>			100N-BG-N			125C-BG-N			
Product Code	209			298			318A			210A			211A			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/4	8										40	67	48	44	67	48
3/8	10										42	68	48	44	69	48
1/2	15	51	137	55	51	137	55	51	150	70	48	69	55	53	77	63
3/4	20	56	157	70	56	158	70	56	173	80	53	81	63	65	99	70
1	25	66	180	70	66	181	70	66	194	80	63	95	70	77	108	80
1 1/4	32	68	216	80	68	216	80	74	228	100	73	104	80	85	137	90
1 1/2	40	74	257	90	74	257	90	84	273	110	81	127	90	100	160	100
2	50	84	296	100	84	297	100	98	313	125	94	147	100	119	179	110
2 1/2	65										115	178	110	150	202	125
3	80										131	200	125	178	242	160
Body	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Bonnet/Cap	Cast Bronze			Cast Bronze			Cast Bronze			Forged Brass			Forged Brass or Cast Bronze			
Stem	Cast Bronze			Cast Bronze			Cast Bronze			Dezincification Resistant Brass			Cast Bronze			
Disc/Ball	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Packing	Aramid Fibers Graphite			Flexible Graphite & Aluminum			Flexible Graphite & Aluminum			Aramid Fibers Graphite			Aramid Fibers Graphite			
Hand Wheel	Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			
Note	Screwed Bonnet Inside Screw			Union Bonnet Inside Screw			Union Bonnet Inside Screw			Screwed Bonnet Inside Screw			Screwed Bonnet Inside Screw			

Type	Globe			Globe			Globe			Globe			Globe			
																
Fig	125C-BD-N			150E-BG-N			150E-BG-NR-NPT<UL1R1>			150E-BG-N-PN25-B62-			150-BD-N			
Product Code	220A			213A			213A			213P			221			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/4	8				44	67	48	44	67	48						
3/8	10	53	87	55	44	69	48	44	69	48						
1/2	15	57	88	63	53	80	63	53	80	63	53	80	63	64	114	63
3/4	20	66	103	70	65	94	70	65	94	70	65	94	70	78	138	90
1	25	76	113	80	77	104	80	77	104	80	77	104	80	90	156	100
1 1/4	32	88	138	90	85	127	90	85	127	90	85	127	90	105	183	110
1 1/2	40	100	154	100	100	145	100	100	145	100	100	145	100	120	186	110
2	50	120	183	110	119	173	110	119	173	110	119	173	110	145	212	125
2 1/2	65	147	210	125	139	199	125	139	199	125						
3	80	162	230	140	158	214	140	158	214	140						
4	100															
Body	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Bonnet/Cap	Forged Brass or Cast Bronze			Forged Brass or Cast Bronze			Forged Brass or Cast Bronze			Forged Brass			Forged Brass or Cast Bronze			
Stem	Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			Dezincification Resistant Brass			
Disc/Ball	R-PTFE			Cast Bronze			Cast Bronze			Cast Bronze			G/F+PTFE			
Packing	Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			Aramid Fibers Graphite			
Hand Wheel	Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			Aluminum Die-Cast			
Disc Holder	Forged Brass												Forged Brass/Cast Bronze			
Note	Screwed Bonnet Inside Screw Union Bonnet(21/2&3)			Screwed Bonnet Inside Screw			Screwed Bonnet Inside Screw			Rising Stem Screwed Bonnet			Union Bonnet Inside Screw			