











Type	Wafer Check 			Strainer 			Strainer 			Strainer Body Marking: Class 150 			Strainer 			
Fig	10-BNW			150-BT-N			150-BT-N-B62-			150-BT-N-PN25-			PN16-BTE			
Product Code				380			380			380P			-			
inch	mm	L	H	D	L	H	H1*	L	H	H1*	L	H	H1*	L	H	H1*
1/4	8															
3/8	10															
1/2	15				80	49	68	80	49	68	80	49	68	65	42	68
3/4	20				100	57	83	100	57	83	100	57	83	80	52	83
1	25				115	70	105	115	70	105	115	70	105	92	60	105
1 1/4	32				135	82	124	135	82	124	135	82	124	110	72	124
1 1/2	40	54	132	55	160	98	149	160	98	149	160	98	149	122	81	149
2	50	56	139	70	195	121	188	195	121	188	195	121	188	150	101	188
2 1/2	65	56	146	70	230	148	216	230	148	216						
3	80	59	152	70	240	180	267	240	180	267						
4	100	66	165	70												
5	125	72	183	70												
6	150	78	208	80												
8	200	96	237	80												
Body	Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			Cast Bronze			
Bonnet/Cap	Forged Brass or Cast Bronze			Forged Brass			Forged Brass			Forged Brass			Forged Brass			
Gasket				Non-Asbestos Sheet			Non-Asbestos Sheet			Non-Asbestos Sheet			Non-Asbestos Sheet			
Screen				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Seat	NBR															
O ring				FKM for 2 1/2 & 3			FKM for 2 1/2 & 3									
Note	FKM or EPDM available By-pass valve mounted			Screwed Cap *Height for removing the screen			Screwed Cap *Height for removing the screen			Screwed Cap End Connection : PN25 *Height for removing the screen			Screwed Cap *Height for removing the screen			

Type	Ball 			Ball 			Ball 			Ball 			Ball 			
Fig	BX-N			BX-N-T			RP-NK			600RC-N			600RC-N-T			
Product Code	5011			5011T			5044A			5026			5026W			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/4	8							42	37	70	50	37	70	50	38	60
3/8	10							42	37	70	50	37	70	50	38	60
1/2	15	56	75	80	56	79	82	53	40	80	65	40	80	65	43	65
3/4	20	65	79	80	65	83	82	60	44	80	68	44	80	68	47	65
1	25	78	83	110	78	90	94	72	50	110	79	50	110	79	57	100
1 1/4	32	86	98	110	86	105	94	84	55	110	86	55	110	86	62	100
1 1/2	40	96	102	110	96	109	94	92	65	150	96	65	150	96	76	120
2	50	109	109	140	109	124	120	110	72	150	109	72	150	109	83	120
2 1/2	65							138	101	200	138	100	200			
3	80							167	103	300	167	112.5	300			
Body	Cast Bronze			Forged Brass			Forged Brass			Forged Brass			Forged Brass			
Stem	Dezincification Resistant Brass			Dezincification Resistant Brass			Brass / Nickel Plated			Brass / Nickel Plated			Brass / Nickel Plated			
Disc/Ball	SCS13A			SCS13A			Brass/Chrome Plated of Stainless steel			Brass / Chrome Plated			Brass / Chrome Plated			
Seat	PTFE			PTFE			PTFE			PTFE			PTFE			
O ring	FKM			FKM			FKM			FKM			FKM			
Note	Standard Bore Long neck for thermal insulation			Standard Bore Long neck for thermal insulation T-Handle			UL/FM/CSA approved (up to 50mm)			Full Bore			Full Bore T-Handle			